



# Adjustment Pads -Space Saving Type-

CAD Data Folder Name: 47\_Casters

Pads (D dimensions) are more compact than the conventional Adjustment Pads.

RoHS

M Material: SS400 or equivalent  
S Surface Treatment: Trivalent Chromate Plating

Screw shafts turns.

Part Number Type	D	M (Coarse)	A			H	l <sub>1</sub>	l <sub>2</sub>	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price
			20	50	100							
HNFJN	28	8	20	50	100	17.7	5.2	6.5	13	6.5	48	387
		12	30	80	100	23	7.4	10	19	13	55	474
	48	8	20	50	100	20.7	5.2	6.5	13	6.5	77	601
		12	30	80	100	23	7.4	10	19	13	90	624
	58	8	20	50	100	20.7	5.2	6.5	13	6.5	121	706
		12	30	80	100	23	7.4	10	19	13	133	724

RoHS

M Material: SS400 or equivalent  
S Surface Treatment: Trivalent Chromate Plating

Screw shafts turns.

Part Number Type	D	M (Coarse)	A			H	l <sub>1</sub>	l <sub>2</sub>	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price
			20	50	100							
HNFJR	28	8	20	50	100	28.2	5.2	6.5	13	6.5	50	451
		12	30	80	100	35.4	7.4	10	19	13	59	546
	48	8	20	50	100	33.2	5.2	6.5	13	6.5	73	697
		12	30	80	100	35.4	7.4	10	19	13	85	715
	58	8	20	50	100	33.2	5.2	6.5	13	6.5	115	801
		12	30	80	100	35.4	7.4	10	19	13	129	819

Order Example: Part Number - **M** - **A**  
**HNFJR48** - **12** - **80**

Delivery: **5** Days **P87**

Price: **Volume Discount Rate** (Round up to the Baht.) **P87**

Qty.	1-49	50-99
Rate	Unit Price	10%

For orders larger than indicated quantity, please request a quotation.

# Adjuster Feet -Rotary Type / Female Thread Socket Type-

CAD Data Folder Name: 47\_Casters

RoHS

M Material: S45C  
S Surface Treatment: Trivalent Chromate  
M Material: SS400 or equivalent  
S Surface Treatment: Trivalent Chromate

Tilttable 15° in all 360° directions.

Part Number Type	M-A	D	D <sub>1</sub>	H	l <sub>1</sub>	l <sub>2</sub>	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price		
										LEMNT	LEMNS	
LEMNT (Steel)	10-75	32	21	22	6	8	17	11.0	342	415	751	
	10-100									433	779	
	12-75									378	506	1,024
LEMNS (Stainless Steel)	12-100	48	23	29	7.5	10	19	16.0	390	533	1,047	
	16-100									430	769	1,547
	16-130									445	792	1,629

Order Example: Part Number **LEMNT16-130**

Price: **Volume Discount Rate** (Round up to the Baht.) **P87**

Qty.	1-19	20-34	35-49	50-99
Rate	Unit Price	5%	10%	18%

For orders larger than indicated quantity, please request a quotation.

Delivery: **5** Days **P87**

- Others: **7** Days

RoHS

M Material: STKM  
S Surface Treatment: Trivalent Chromate Plating

Approx. 30°

When a leg has an angle.  
When floor surface is curved.

Part Number Type	M (Coarse)	A	L	D	B	E	Allowable Vertical Load (kN)	Mass (g)	Unit Price
FJRP	6	14	31	25	8	9.7	0.59	11	96
	8	19	37.5	30	10	11.2	1.08	21	101
	10	20	42.5	40	13	13.7	1.57	38	128
	12	25	51	50	17	16	3.14	70	151

Part Number Type	M (Coarse)	B	C	D	E	H	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
									LEMN	LEMS
LEMN (Nylon)	10	9.5	39.0	50	18	16	15.9	17.1	214	255
	12	12.7	41.0						301	
	16	14.2	44.5							

Order Example: Part Number **LEMN10**

Delivery: **1** Day **5** Days **P87**

Price: **Volume Discount Rate** (Round up to the Baht.) **P87**

Qty.	1-19	20-34	35-49	50-99
Rate	Unit Price	5%	10%	18%

For orders larger than indicated quantity, please request a quotation.

Delivery: **5** Days **P87**

- Others: **7** Days