

# Dowel Pins

## Oversized

**■ Straight**

Type	Material	Hardness
MS	SUJ2	58HRC~
MSC	SUS440C	58HRC~
MSCSS	SUS304	-

⚠ l1 dimension may become larger than the value shown in the catalog due to polishing process.

l1	Part Number		L	Unit Price	Volume Discount Rate
	Type	D			
0.4	MS	1	6 8 10	1~499	500~2000
0.6		1.5	6 8 10		
1		2	6 8 10 15 20		
		2.5	6 8 10 15 20 25 30		
1.5		3	6 8 10 15 20 25 30 35 40		
		4	8 10 15 20 25 30 35 40 45 50		
2		5	8 10 15 20 25 30 35 40 45 50		
2.5		6	8 10 15 20 25 30 35 40 45 50 55 60		
		8	10 15 20 25 30 35 40 45 50 55 60 65 70 80		
3		10	15 20 25 30 35 40 45 50 55 60 65 70 80		
3.5		12	20 25 30 35 40 45 50 55 60 70 80		
		13	30 40 50 60 70 80		

☐ For orders of 1 ~ 9 pc(s): Unit Price + Low Quantity Surcharge (1 Line Item) ⚠ For orders larger than indicated quantity, please check with WOS.

l1	Part Number		L	Unit Price	Volume Discount Rate			
	Type	D			1 ~ 9 pc(s)	10~49	50~99	100~2000
0.4	MSC	1	5 6 8 10					
0.6		1.5	5 6 8 10					
1		2	5 6 8 10 12 15 20					
		2.5	6 8 10 12 15 20					
1.5		3	6 8 10 12 15 20 25 30					35 40
		4	8 10 12 15 20 25 30					35 40 50
2		5	8 10 12 15 20 25 30					35 40 50
		6	8 10 12 15 20 25 30					35 40 50 60
2.5		8	10 15 20 25 30					35 40 50 60
3		10	10 15 20 25 30					35 40 50 60
3.5		12	30 35 40 50 60					

⚠ For orders larger than indicated quantity, please check with WOS.

l1	Part Number		L	Unit Price	Volume Discount Rate		
	Type	D			1 ~ 9 pc(s)	10~49	50~99
0.4	MSCSS	1	5 6 8 10				
0.6		1.5	5 6 8 10				
1		2	5 6 8 10 12 15				
		2.5	6 8 10 12 15				
1.5		3	6 8 10 12 15 20				
		4	8 10 12 15 20				
2	5	10 12 15 20					
	6	10 12 15 20 25					

⚠ For orders larger than indicated quantity, please check with WOS.

**■ Straight, Chamfered**

RoHS10

Type	Material	Hardness
MSCM	SUS440C	58HRC~
MSCSM	SUS304	-

C	Part Number		L	Unit Price	Volume Discount Rate		
	Type	D			1 - 19 pc(s)	20~29	30~49
0.3 or Less	MSCM	2	6 8 10 12 15				
		3	10 12 15 20				
		4	10 12 15 20				
0.5	MSCM	5	10 12 15 20				
		6	10 12 15 20 25				

⚠ For orders larger than indicated quantity, please check with WOS.

C	Part Number		L	Unit Price	Volume Discount Rate		
	Type	D			1 - 19 pc(s)	20~29	30~49
0.3 or Less	MSCSM	2	6 8 10 12 15				
		3	10 12 15 20				
		4	10 12 15 20				
0.5	MSCSM	5	10 12 15 20				
		6	10 12 15 20 25				

⚠ For orders larger than indicated quantity, please check with WOS.

**■ Straight - High Precision**

Type	Material	Hardness
MSV	SUJ2	58HRC~
MSVC	SUS440C	58HRC~



⚠ Measurement is taken place in constant temperature room.  
⚠ l1, l2 dimension may become larger than the value shown in the catalog due to polishing process.

l1	l2	Part Number		L	Unit Price	Volume Discount Rate		
		Type	D			1~49	50~499	500~2000
1	0.2	MSV	2	6 8 10				
			3	8 10 15 20 25 30				
			4	10 15 20 25 30				
	0.5		5	10 15 20 25 30				
			6	10 15 20 25 30				
			8	20 30 40				
3	10	30 40 50 60						

☐ For orders of 1 ~ 9 pc(s): Unit Price + Low Quantity Surcharge (1 Line Item) ⚠ For orders larger than indicated quantity, please check with WOS.

l1	l2	Part Number		L	Unit Price	Volume Discount Rate		
		Type	D			1~9 pc(s)	10~49	50~99
0.4	0.1	MSVC	1	5 6 8 10				
			0.6	1.5				
1	0.2		2	5 6 8 10				
			3	6 8 10 15 20 25 30				
1.5	0.5		4	8 10 15 20 25 30				
			5	10 15 20 25 30				
2	6	10 15 20 25 30						
2.5	8	20 30 40						
3	10	30 40 50 60						

⚠ For orders larger than indicated quantity, please check with WOS.  
For orders larger than indicated quantity, please request a quotation. P99

Ordering Example

Part Number	-	L
MS2	-	10
MSCM4	-	12
MSV2	-	6