

Rods

Material: Stainless Steel, Aluminum, Brass, Pure Titanium Class 2

Rods		Material
O.D. Selectable	O.D. Configurable	
RDOF	-	SUS303
RDOS	FRDOS	SUS304
RDOH	-	SUS316
RDOA	-	A2017
RDOK	-	A5056
RD52A	-	A5052
RDOG	-	C3604-LCD (Brass with Low Cadmium)
RDOT	-	Pure Titanium Class 2

or More	or Less	C
D3	D16	0.5
D17	D80	1.0

or More	or Less	Tolerance
10	30	±0.2
31	120	±0.3
121	400	±0.5
401	1000	±0.8

RoHS 10

Rods (O.D. Selectable)

Part Number Type	D	L 1mm Increment
RDOF RDOS RDOH RDOA RDOK RD52A (D5~12, 15~20) RDOG RDOT (D3~6)	3	
	4	10~250
	5	
	6	
	8	10~500
	10	
	12	
	13	10~750
	15	
	16	10~900
18		
20	20~1000	
25		
30		
RDOF RDOS	50	30~1000
	60	
	80	30~200



Ordering Example

Rods (O.D. Selectable)

Part Number - L
RDOA15 - 700

Rods (O.D. Configurable)

Part Number - D - L
FRDOS - D11 - L113

Rods (O.D. Configurable)

Part Number	D 1mm Increment	L 1mm Increment
FRDOS	6~10	10~500
	11~15	10~750
	16~17	10~900
	18~30	20~1000



Alterations

Part Number - L - (MC, WMC)
RDOF20 - 535 - MC8

O.D. Tolerance

Part Number D	RDOF RDOS	FRDOS RDOH RDOT	RDOA	RDOK RD52A RDOG
3				
4				
5				
6				
8				
10				
12	0	0	±0.1	
13	-0.1	-0.1		±0.1
15				
16			±0.3	
18				
20				
25				
30			±0.4	
50	0			
60	-0.2			
80				

Alterations	One End Tapped	Both Ends Tapped
Code	MC	WMC
Spec.	Adds a tap on one end. Ordering Code MC8 6 ≤ D ≤ 30 When L ≤ Mx2, the tap goes through. D MC (Selection Range) 6, 7 3 8, 9 3, 4 10, 11 3, 4, 5 12~14 3, 4, 5, 6 15~19 3, 4, 5, 6, 8 20~24 3, 4, 5, 6, 8, 10, 12 25~30 3, 4, 5, 6, 8, 10, 12, 16 When L ≤ Mx4, the pilot hole for tapping may go through.	Adds taps on both ends. Ordering Code WMC12 6 ≤ D ≤ 30 When L ≤ Mx4, the tap goes through. D WMC (Selection Range) 6, 7 3 8, 9 3, 4 10, 11 3, 4, 5 12~14 3, 4, 5, 6 15~19 3, 4, 5, 6, 8 20~24 3, 4, 5, 6, 8, 10, 12 25~30 3, 4, 5, 6, 8, 10, 12, 16

Rods (O.D. Selectable)

Part Number Type	D	Unit Price					
		Min. L - 100	101-200	201-400	401-600	601-800	801-1000
RDOF (SUS303)	3						
	4						
	5						
	6						
	8						
	10						
	12						
	13						
	15						
	16						
	18						
	20						
	25						
	30						
	50						
60							
80							
RDOS (SUS304)	3						
	4						
	5						
	6						
	8						
	10						
	12						
	13						
	15						
	16						
	18						
	20						
	25						
	30						
	50						
60							
80							
RDOH (SUS316)	3						
	4						
	5						
	6						
	8						
	10						
	12						
	13						
	15						
	16						
	18						
	20						
	25						
	30						
	RDOA (A2017)	3					
4							
5							
6							
8							
10							
12							
13							
15							
16							
18							
20							
25							
30							

For maximum L dimension in each D dimension, refer to the specification table shown on the left-hand page.

Part Number Type	D	Unit Price					
		Min. L - 100	101-200	201-400	401-600	601-800	801-1000
RDOK (A5056)	3						
	4						
	5						
	6						
	8						
	10						
	12						
	13						
	15						
	16						
RD52A (A5052)	5						
	6						
	8						
	10						
	12						
	15						
RDOG (C3604-LCD)	3						
	4						
	5						
	6						
	8						
	10						
	12						
	13						
	15						
	16						
RDOT (Pure Titanium Class 2)	3						
	4						
	5						
	6						
	8						
	10						
FRDOS (SUS304)	6~10						
	11~15						
	16~19						
	20~24						
	25~27						
	28~30						

Rods (O.D. Configurable)

Part Number	D 1mm Increment	Unit Price					
		Min. L - 100	101-200	201-400	401-600	601-800	801-1000
FRDOS (SUS304)	6~10						
	11~15						
	16~19						
	20~24						
	25~27						
	28~30						