
















Plastic Joint

PJ300B~PJ507


RoHS 10 PJ300B~PJ401















PJ300B		
PJ301		
PJ302A		
PJ302B		
PJ303		
PJ400		
PJ401		

Part Number	Color	Mass (g)	Unit Price (1-19 pcs)	Volume Discount Rate (20-49)	Volume Discount Rate (50-99)	Volume Discount Rate (100-200)
PJ300B		18				
PJ301	W (White)	18				
PJ302A	S (Gray)	30				
PJ302B		29				
PJ303		29				
PJ400	S	45				
PJ401	W, S	30				


RoHS 10 PJ403~PJ500

















PJ403		
PJ404		
PJ405		
PJ408A		
PJ409		
PJ500		

Part Number	Color	Mass (g)	Unit Price (1-19 pcs)	Volume Discount Rate (20-49)	Volume Discount Rate (50-99)	Volume Discount Rate (100-200)
PJ403	W, S	30				
PJ404	S	45				
PJ405	S	32				
PJ408A		43				
PJ409	W, S	47				
PJ500		4.5				

RoHS 10 PJ501~PJ507



PJ501		
PJ502		
PJ503		
PJ504		
PJ505		
PJ506 (Set of 2)		
PJ507		

Part Number	Color	Mass (g)	Unit Price (1-19 pcs)	Volume Discount Rate (20-49)	Volume Discount Rate (50-99)	Volume Discount Rate (100-200)
PJ501		8				
PJ502		15				
PJ503	W (White)	3				
PJ504	S (Gray)	3				
PJ505		19				
PJ506*		6				
PJ507		6				


* PJ506 is in set of 2 pieces.

















Ordering Example: Part Number - Color
PJ301 - S

Plastic Joint

PJ600~PJ708


RoHS 10 PJ600~PJ607



















PJ600		
PJ601L		
PJ601R		
PJ602		
PJ603L		
PJ603R		
PJ604		
PJ607		

Part Number	Color	Mass (g)	Unit Price (1-19 pcs)	Volume Discount Rate (20-49)	Volume Discount Rate (50-99)	Volume Discount Rate (100-200)
PJ600		32				
PJ601L		39				
PJ601R	W (White)	39				
PJ602	S (Gray)	58				
PJ603L		65				
PJ603R		65				
PJ604		49				
PJ607		64				

RoHS 10 PJ700A~PJ705












PJ700A		
PJ700B		
PJ701		
PJ702		
PJ703		
PJ704A		
PJ704B		
PJ705		


Part Number	Color	Mass (g)	Unit Price (1-19 pcs)	Volume Discount Rate (20-49)	Volume Discount Rate (50-99)	Volume Discount Rate (100-200)
PJ700A		21				
PJ700B		19				
PJ701	W (White)	23				
PJ702	S (Gray)	32				
PJ703		14				
PJ704A		19				
PJ704B		17				
PJ705		21				

Ordering Example: Part Number - Color
PJ600 - S

RoHS 10 PJ706~PJ708



PJ706		
PJ706B		
PJ707		
PJ708		

* PJ203B is used in the following case.
-Frame Connection

(Do not use in places where forces may be applied.)

Part Number	Color	Mass (g)	Unit Price (1-19 pcs)	Volume Discount Rate (20-49)	Volume Discount Rate (50-99)	Volume Discount Rate (100-200)
PJ706	W, S	13				
PJ706B*	W	12				
PJ707	W, S	18				
PJ708		26				

* PJ706B is available in W (White) only.