

Comparison Points with Similar Products | Replacement Cycle (Reference) : 100,000 times Convenient package sale is available at a low price.

**Double Tipped Probe**  
Sold by the package (50 pcs./pkg.)

**RNPA020**

Part	Material	Surface Treatment
(1) Plunger	SK4	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SUS304	Gold Plating

**Double Tipped Probe**  
Sold by the package (50 pcs./pkg.)

**RNPA026**

Part	Material	Surface Treatment
(1) Plunger	SK4	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SUS304	Gold Plating

**Double Tipped Probe**  
Sold by the package (50 pcs./pkg.)

**RNPC026**

Part	Material	Surface Treatment
(1) Plunger	BeCu	Gold Plating on Nickel Undercoat
(2) Barrel	Phosphor Bronze	Gold Plating on Nickel Undercoat
(3) Spring	SWP	Gold Plating

Part Number	Type	No.	Tip Shape		Mounting Pitch (min)	Full Stroke	Spring Pressure (2/3 Stroke)	Allowable Current	Resistance	Replacement Cycle (Reference)	Unit Price (50 pcs./pkg.)
			Left Side	Right Side							
RNPA	020		B	U, B, J	0.3mm	1.1mm	12±3gf	0.5A	100mΩ	100,000 times	
			J1	U, J							
RNPA	026		B	U, B, J	0.35mm	1.1mm	16±5gf	0.5A	180mΩ	100,000 times	
			J1	U, J							
RNPC	026		B	B	0.35mm	0.8mm	21±5gf	0.5A	180mΩ	100,000 times	

Ordering Example: Part Number (Type, No.) - L R  
RNPA020 - B J