


OUTSIDE RINGS FOR PL EXCHANGE TYPE



Outside ring

| D | Dm6 | Dh7 | L | E | a | b |
|----|-----|-----|----|------|-----|-----|
| 4 | 4 | 4 | 8 | 2.8 | 1.0 | 1.2 |
| 5 | 5 | 5 | 8 | 2.85 | 1.0 | 1.2 |
| 6 | 6 | 6 | 8 | 2.9 | | 1.2 |
| 8 | 8 | 8 | 10 | 3.4 | 1.0 | 1.5 |
| 10 | 10 | 10 | 12 | 4.2 | | |
| 12 | 12 | 12 | 14 | 4.4 | 1.2 | 1.8 |
| 16 | 16 | 16 | 14 | 5.0 | 1.4 | |
| 20 | 20 | 20 | 16 | 5.3 | 1.5 | 2.0 |

⚠ Inside arrows on this page are adapted for combination with outside rings of date marked pin sets on P.107 and P.108, and products on P.109.

☑ SUS420F
☑ 50~55HRC

Month · Day · No-marking Type

| Indication | Outside rings divisions | Part No. | | D | Indication | Outside rings divisions | Part No. | | D |
|-----------------|-------------------------|----------|----|----|-----------------|-------------------------|----------|----|----|
| | | Type | D | | | | Type | D | |
| Month | 12 uniform divisions | C-DTDX-R | 4 | 12 | Day (2nd digit) | 12 uniform divisions | C-DTFX-R | 4 | 12 |
| | | | 5 | | | | | | |
| | | | 6 | | | | | | |
| | | | 8 | | | | | | |
| | | | 10 | | | | | | |
| | | | 12 | | | | | | |
| Day (1st digit) | 12 uniform divisions | C-DTEX-R | 4 | 10 | Day | 31 uniform divisions | C-DTGX-R | 16 | 16 |
| | | | 5 | | | | | | |
| | | | 6 | | | | | | |
| | | | 8 | | | | | | |
| | | | 10 | | | | | | |
| | | | 12 | | | | | | |
| No-marking | 10 uniform divisions | C-DTNX-R | 4 | 10 | No-marking | 12 uniform divisions | C-DTNX-R | 4 | 10 |
| | | | 5 | | | | | | |
| | | | 6 | | | | | | |
| | | | 8 | | | | | | |
| | | | 10 | | | | | | |
| | | | 12 | | | | | | |

Order

Part No.
C-DTDX-R16

Days to Ship **10** Days

Price

Order / Quote:
WOS: <https://in.misumi-ec.com/>
TEL:+91-124-468-8800 E-mail:cs@misumi.co.in

Character Designation Type

| Indication | | | | | | | |
|-----------------------------|-----------------------------|-----------------------------|-----------------------------|-----------------------------|-----------------------------|-----------------------------|-----------------------------|
| 1M (1 place) | 2M (2 places) | 3M (3 places) | 4M (4 places) | 5M (5 places) | 6M (6 places) | 10M (10 places) | 12M (12 places) |
| Engraving position ① | Engraving position ① | Engraving position ① | Engraving position ① | Engraving position ① | Engraving position ① | Engraving position ① | Engraving position ① |

Up to 1~3 characters can be designated at each engraving position. Up to 1~2 characters can be designated at each engraving position. Up to 1 character can be designated at each engraving position.

| Type | Part No. | | Engraving characters (1~3 characters-Characters printed in blue in indications) | | | | | | | | | | | | | | | | | | |
|---------|------------|----|---|---|---|---|---|---------|--------------------------|------------|--|--|--|--|--|--|--|--|--|--|--|
| | Indication | D | Engraving position ①~⑫ | | | | | | | | | | | | | | | | | | |
| C-DTX-R | 1M | 4 | 1 | 2 | 3 | 4 | 5 | Name | Characters for engraving | Order code | | | | | | | | | | | |
| | 2M | 5 | 6 | 7 | 8 | 9 | 0 | Slash | / | ¥ | | | | | | | | | | | |
| | 3M | 6 | A | B | C | D | E | Greater | > | > | | | | | | | | | | | |
| | 4M | 8 | F | G | H | I | J | Less | < | < | | | | | | | | | | | |
| | 5M | 10 | K | L | M | N | O | Plus | + | + | | | | | | | | | | | |
| | 6M | 12 | P | Q | R | S | T | Minus | - | # | | | | | | | | | | | |
| | 10M | 12 | U | V | W | X | Y | Space | | % | | | | | | | | | | | |
| 12M | 16 | Z | | | | | | | | | | | | | | | | | | | |

⚠ Use ¥ for indicating / (slash), # for - (minus), and % for % (space). ☒ Not applicable to D4 and D5 of 5M, 6M and 10M.

Order

Part No.

① Characters for engraving

② Characters for engraving

③ Characters for engraving

④ Characters for engraving

⑤ Characters for engraving

⑥ Characters for engraving

⑫ Characters for engraving

C-DTX-R 3M 6

C-DTX-R 6M 16

C-DTX-R 12M 16

POM

PS

SAN

19

20

21

22

23

24

%

1

2

3

4

5

F

12 uniform divisions

10 uniform divisions

Days to Ship **10** Days

Price

Order / Quote:
WOS: <https://in.misumi-ec.com/>
TEL:+91-124-468-8800 E-mail:cs@misumi.co.in

⚠ C-VALUE PL exchange type products involve third-party intellectual property rights, so litigation claims may be raised against customers who bring them to Japan, the United States, Italy, Germany or France.

Date Mark Inserts