

NEW

AIR MICRO GRINDERS

AIR MICRO GRINDER / 3 MM, 6MM COLLET / HIGH DURABILITY MODEL

shows in red

■ Application Use together with the rubber grindstone with shaft for mold, etc.

■ Air Micro Grinder

M-AMGR



Body length	Collet	Allowable rotational speed (rpm)	Supply air pressure (MPa)	Fitting	Hose length	Part Number	Unit Price 1~5 pcs
130	3	30000	0.6	1/4	1300	M-AMGR	Quotation



Order

Part Number
M-AMGR



Days to Ship

Quotation



Price

Quotation

■ Air Micro Grinder (3 mm, 6 mm Collet)

M-GP8240D



■ Features

- Can be used for both 3 mm shaft and 6 mm shaft with various grindstones.

Body length	Collet	Allowable rotational speed (rpm)	Supply air pressure (MPa)	Fitting	Hose length	Part Number	Unit Price 1~3 pcs
130	3 or 6	35000	0.6	1/4	1500	M-GP8240D	Quotation



Order

Part Number
M-GP8240D



Days to Ship

Quotation



Price

Quotation

■ Air Micro Grinder (High Durability Model)

M-GP8246C



■ Features

- With 5 built-in bearings (2 in general), it withstands high load, achieving smooth and stable rotation.
- Rubber grip helps reducing long-term work fatigue.

Body length	Collet	Allowable rotational speed (rpm)	Supply air pressure (MPa)	Fitting	Hose length	Part Number	Unit Price 1~5 pcs
135	3	60000	0.6	1/4	1300	M-GP8246C	Quotation



Order

Part Number
M-GP8246C



Days to Ship

Quotation



Price

Quotation

MOLD MAINTENANCE
RELATED PRODUCTS