


RUBBER HOSES FOR HIGH-TEMPERATURE WATER / HOSE FOR HOT WATER / HOSE BANDS

■ Rubber Hose for High-Temperature Water



KGH (Rubber hose for high-temperature water)




Applicable for liquid-water

Internal / Outside rubber		Reinforcing wire
Heat resistant synthetic rubber (EPDM)		Aramid fiber

D	d	Part Number		L (unit: m)	Unit Price (1~9 pcs)						Maximum allowable pressure MPa (kgf/cm ²)	Allowable temperature range °C	Minimum bending radius mm	Mass kg/m
		Type	No.		L1	L2	L5	L10	L20	L30				
18	9.7	KGH	3	1 2 5 10 20 30	Quotation						1.0(10.2)	-30~120	120	0.23

☎ To be quoted on price & lead time above Max. Q'ty.

🔍 Check the size of the outer diameter of the hose nipple in use. Although the inner diameter (d) of the hose is 9.7, applicable for hose nipple of outer diameter between 9.7 and 12mm.



Notes

- When installing the hose nipple, fix it with a hose band (MHBS).
- This product is for warm water use. NEVER use it with oil.
- Do not use the hose in an environment where it is likely to come into contact with oil.
- Inspect the hose periodically, and if it shows signs of cracking, hardening or other changes, replace them.
- Allow a certain margin of length as the hose will expand or contract depending on whether it is pressurized or depressurized.



Order

Quotation



Days to Ship

Quotation



Price


Quotation

■ Hose for Hot Water



RoHS 10

MHW (Hose for hot water)



Applicable for liquid-water

Soft vinyl chloride

D	d	Part Number		L (unit: m)	Unit Price (1~9 pcs)			Part Number	Specifications			
		Type	No.		L10	L20	L50		Allowable pressure kPa (kgf/cm ²)	Destructive pressure kPa (kgf/cm ²)	Min. bend radius (room temp.)	Allowable temperature range
13.5	8	MHW	1	10 20 50	Quotation			MHW1	0~1000(0~10)	5500(55)	56	0~60°C
18	12		2					MHW2	0~800(0~8)	4000(40)	84	
22	15		3					MHW3	0~800(0~8)	6000(60)	105	



Order

Part Number

MHW2

L

10



Days to Ship

Quotation



Price

Quotation

■ Hose Band

MHBT

RoHS 10



M SUS430
Safety cap: PE
Bolt: SWCH10K

External hose (mm)	Max. tightening torque	Part Number		Unit Price
Diameter	N · cm {kgf · cm}	Type	No.	1~9 pcs
φ 13~20	350{35}	MHBT	1	Quotation
φ 18~25			2	



Order

Part Number

MHBT1



Days to Ship

Quotation



Price

Quotation

■ Features

MHBT has a safety cap to protect you from getting hurt.