


Equivalent to  
SKD61  
+  
Nitridation Treatment

# STRAIGHT EJECTOR PINS

Green character items  
now kept in stock.

Standard Spec.



Guaranteed range of shaft-diameter precision (b1=L-x1)  
T4 xC 1 max.40  
JIS C x1max.40  
Material: Equivalent to SKD61+ Nitridation Treatment  
Hardness: Surface: 900HV- Material: 40-45HRC

Model	Shoulder Thickness	Tolerance (T)	Tolerance of P Dimensions			
C-EPN	4 mm. (T4)	$\begin{matrix} 0 \\ -0.02 \end{matrix}$ (L>300 $\rightarrow$ $\begin{matrix} 0 \\ -0.05 \end{matrix}$ )	L \ P	1~13	15~20	25
C-EPJ	6.8 mm. (JIS)	$\begin{matrix} 0 \\ -0.05 \end{matrix}$	L ≤ 600	$\begin{matrix} -0.01 \\ -0.02 \end{matrix}$	$\begin{matrix} -0.01 \\ -0.03 \end{matrix}$	$\begin{matrix} -0.01 \\ -0.04 \end{matrix}$
			L ≥ 600	$\begin{matrix} -0.01 \\ -0.03 \end{matrix}$	$\begin{matrix} -0.01 \\ -0.03 \end{matrix}$	$\begin{matrix} -0.01 \\ -0.05 \end{matrix}$

Shoulder Thickness 4mm		Shoulder Thickness JIS		Model		L Selection										U/price						
H	T	H	T	Type	P																	
3				C-EPN	1	100	150															
4					1.5	100	150	200														
5					2	100	150	200	250	300	350	400										
6					2.5	100	150	200	250	300	350	400										
7					3	100	150	200	250	300	350	400	450	500								
8		8			3.5	100	150	200	250	300	350	400	450	500								
9	4	9	6		4	100	150	200	250	300	350	400	(500)									
10		10			4.5	100	150	200	250	300	350	400	(500)									
11		11			5	100	150	200	250	300	350	400	500	(600)								
15		15			5.5	100	150	200	250	300	350	400	500									
17		17			6	100	150	200	250	300	350	400	500	(600)	(700)							
18		18			6.5	100	150	200	250	300	350	400	500	(600)	(700)							
20		20			7	100	150	200	250	300	350	400	500	(600)	(700)	(800)	(900)	(1000)				
21		21		8	100	150	200	250	300	350	400	(450)	500	(600)	(700)	(800)	(900)	(1000)				
25		25		10	100	150	200	250	300	350	400	(450)	500	(600)	(700)	(800)	(900)	(1000)				
30		30		12	100	150	200	250	300	350	400	(450)	500	(600)	(700)	(800)	(900)	(1000)				
				(13)	100	150	200	250	300	350	400	500										
				15	100	150	200	250	300	350	400	(450)	500	(600)	(700)	(800)	(900)	(1000)				
				16	100	150	200	250	300	350	400	500	(600)	(700)	(800)	(900)	(1000)					
				20		150	200	250	300	400		500	600	700	800	900	1000					
				25			200	300	400		500	600	700	800	900	1000						

Quotation via WOS

⊕ P dimension in "( )" only applicable to C-EPN spec.  
⊕ L dimension in "( )" only applicable to C-EPJ spec.



Part Number — L  
C-EPN3 — 100



Delivery 1 Day



Price Contact Information for Inquiry  
WOS: <http://th.misumi-ec.com/>  
TEL: 038-959-200 FAX: 038-959-202

ส่วนลดตามจำนวนซื้อ สามารถตรวจสอบราคาได้ที่ WOS

\*\*\*Ejector Pins บางขนาดที่อยู่ในกรอบสีเทายังไม่จำหน่ายในประเทศไทย หากท่านมีความประสงค์ให้มีจัดเก็บสินค้าเพื่อจำหน่ายในประเทศไทย กรุณาแจ้งความจำนงค์ได้... E-mail address: [Moldsales@misumi.co.th](mailto:Moldsales@misumi.co.th)


Dear value customer, some Ejector Pins diameter and size in grey boxes are not available in Thailand. If you would like MISUMI to stock any particular specification please contact us at... E-mail address: [Moldsales@misumi.co.th](mailto:Moldsales@misumi.co.th)

Equivalent to  
SKD61  
Shoulder Thickness  
4mm.

# STRAIGHT EJECTOR PINS

Green character items  
now kept in stock.

Standard Spec.



Model	Shoulder Thickness	Tolerance (P)
C-EPD	4 mm. (T4)	-0.01 -0.02

Guaranteed range of shaft-diameter precision (b1=L-x1)  
x1 max.=40  
Material : Equivalent to SKD61  
Hardness : 50~55HRC

H	T	Model		L				U/price	
		Type	P						
3	4	C-EPD (P <sup>-0.01</sup> -0.02)	1.5	100	150	200			
4			2	100	150	200	250		
5			2.5	100	150	200	250		
6			3	100	150	200		300	
7			3.5	100	150	200		300	
			4	100	150	200		300	
			4.5	100		200		300	
8			5	100	150	200	300	400	500
9			5.5	100		200	300	400	500
			6	100	150	200	300	400	500
10			6.5	100		200	300	400	500
			7	100	150	200	300	400	500
11			8	100	150	200	300	400	500
14			9	100		200	300	400	500
15			10	100	150	200	300	400	500
17			12	100		200	300	400	500
18			13			200	300	400	500

Quotation via WOS



Order

Part Number — L

C-EPD 3 — 150



Delivery

1 Day

ส่วนลดตามจำนวนซื้อ สามารถตรวจสอบราคาได้ที่ WOS



Price

Contact Information for Inquiry

WOS: <http://th.misumi-ec.com/>

TEL: 038-959-200 FAX: 038-959-202

\*\*\*Ejector Pins บางขนาดที่อยู่ในกรอบสีเทายังไม่มียกจำหน่ายในประเทศไทย หากท่านมีความประสงค์ให้มีชุดจัดเก็บสินค้าเพื่อจำหน่ายในประเทศไทย กรุณาแจ้งความจำนงได้ที่... E-mail address: [Moldsales@misumi.co.th](mailto:Moldsales@misumi.co.th)

Dear value customer, some Ejector Pins diameter and size in grey boxes are not available in Thailand. If you would like MISUMI to stock any particular specification please contact us at... E-mail address: [Moldsales@misumi.co.th](mailto:Moldsales@misumi.co.th)