


		7		6		5		4		3		2		1							
		ITEM NO.		PRODUCT CODE		MAT'L		COLOR		QTY		ITEM NO.		PRODUCT CODE		MAT'L		COLOR		QTY	
H		45		HHPFDLN6-5		A6063		Natural		2		1		NEFS6-30120-540		A6063S-T5		Clear		1	
		46		HHPFDRN6-5		A6063		Natural		2		2		NEFS6-3030-243-X8-AV12-BV231		A6063S-T5		Clear		2	
		47		HHPFLN6-SET		A6063		Natural		2		3		NEFS6-3030-277-X8-AV12-BV265		A6063S-T5		Clear		2	
		48		HHPSN6-SST		A6063-T5		Natural		2		4		NEFS6-3030-540		A6063S-T5		Clear		10	
		49		UPCNAT93.5		SUS304		Natural		2		5		NEFS6-3030-581-LTP-RTP		A6063S-T5		Clear		4	
		50		FNT6		SUS304		Natural		4		6		NEFS6-3030-740		A6063S-T5		Clear		8	
		51		ACAE-1100-1100-5		Acrylic		Clear		5		7		NEFS6-3060-540		A6063S-T5		Clear		1	
G												8		NEFS6-3090-540		A6063S-T5		Clear		1	
												9		NFST5-2020-325.5		A6063S-T5		Clear		4	
												10		NFST5-2020-646		A6063S-T5		Clear		4	
												11		NFSR6-3030-1397		A6063S-T5		Clear		4	
												12		NFJN12-150		SS400		Natural		4	
												13		HBLBS6		S45C		Clear		8	
F												14		HBLFSN6-C-SET		ADC12		Clear		20	
												15		HBLFSN6-SET		ADC12		Clear		48	
												16		HBLTS5-C-SET		ADC12		Clear		8	
												17		BCBFS5-10		SUS304		Natural		40	
												18		BCBFS5-15		SUS304		Natural		16	
												19		CBM6-12		Steel		Natural		30	
E												20		FB5-8		Steel		Natural		8	
												21		FB6-10		Steel		Natural		8	
												22		SHFBS4-12		ADC12		Clear		4	
												23		HFC5-2020-B		Polyamide		Black		8	
												24		HFC6-3030-B		Polyamide		Black		8	
												25		HFCR6-3030-B		Polyamide		Black		4	
D												26		HFAFSH6		Steel		Natural		2	
												27		HCJ6		Steel		Natural		8	
												28		HSCA6-B		PE		Black		11	
												29		HMEN6-5		SUS304		Natural		2	
												30		HMENF6-6		SUS304		Natural		1	
												31		HNTT5-5		Steel		Natural		8	
												32		HNTT6-5		Steel		Natural		12	
												33		HNTT6-6		Steel		Natural		36	
C												34		HNTTSN6-4		SUS316		Natural		4	
												35		C-UPCA90		ABS		Black		2	
												36		CBM6-18		Steel		Natural		4	
												37		UWAUNS90		SUS304		Natural		2	
												38		C-FMJ60-N		AL Alloy		Black		4	
												39		HSCP3H-B-6		Resin		Black		1	
												40		HCBR5		Polyamide		Light Gray		4	
												41		HCBR6		Polyamide		Light Gray		12	
B												42		HAJP6-12		SS400		Clear		4	
												43		HFHRF6-3030-540		A6N01SS-T5		Clear		2	
												44		UWASND100		SUS304		Natural		2	
A																					



UNIT: MM

RANK	TOL.
LESS 30 mm	±0.2
OVER 30 to 120 mm	±0.3
OVER 120 to 400 mm	±0.5
OVER 400 to 1000 mm	±0.8
OVER 1000 to 2000 mm	±1.2
OVER 2000 to 4000 mm	±2

MISUMI (THAILAND) CO., LTD.

Company Confidential
 This drawing and any information or descriptive material set out on it are the LEGAL OWNER confidential and copyright property of MISUMI (Thailand) Co., Ltd. © and MUST NOT BE DISCLOSED, COPIED, LOANED in whole or part or used for any purpose without the written permission of MISUMI (Thailand) Co., Ltd.

APPROVED	CHECK BY	1	First design	24/5/2024	TAEY
		0	RECORD	DATE	ISSUE
CU'S REFERENCE/JOB NAME					SHEET
PRODUCT CODE/ DRAWING NO.					1/1
RUNNING#					REV.
Org. date					A
					24/5/2024