



Note that, for some of the types shown here, order might be unable to be received by the MISUMI Malaysia, Indonesia and/or India offices.

Pre-Assembly Insertion Nuts / Stoppers for Aluminum Extrusions - Others For 5 Series (Slot Width 6mm)



Post-Assembly Insertion Nuts / Stoppers for Aluminum Extrusions - Standard For 5 Series (Slot Width 6mm)



Pre-Assembly Insertion Lock Nut

HNTC5

Material: S10C Equivalent
Surface Treatment: Trivalent Chromate

Reference Tightening Torque (N·m)
M S10C Equivalent: 6.8

Part Number	M	Accessory	Unit Price			
			1 - 499 pc(s)	500-749	750-999	1000-1500
HNTC5	5	M4x4 Set Screw for Locking 1 pc.				

Pre-Assembly Insertion Lock Nut

The position of post-assembly insertion lock nuts can be fixed temporarily with the set screw.

Ordering Example: Part Number HNTC5 - M 5

Overall length is shorter than Pre-Assembly Insertion Nuts HNTT. Suitable for installing sensors or other components closely together. Stopper is not included.

Pre-Assembly Insertion Short Nuts

HNTJ5 PACK-HNTJ5

Material: S10C Equivalent
Surface Treatment: Trivalent Chromate

Reference Tightening Torque (N·m)
M S10C Equivalent: 6.8

Part Number	M	HNTJ5				PACK-HNTJ5		
		Unit Price				Unit Price		
		1 - 499 pc(s)	500-749	750-999	1000-1500	1 - 9 pkg(s)	10-19	20-30
HNTJ5 PACK-HNTJ5	3 4 5							

Ordering Example: Part Number HNTJ5 - M 5

Pre-Assembly Insertion Square Nuts

HNKK5

Material: SPCC
Surface Treatment: Trivalent Chromate

Part Number	M	Unit Price		
		1 - 9 pkg(s)	10-19	20-30
HNKK5	3 4 5			

Pre-Assembly Insertion Nuts

Ordering Example: Part Number HNKK5 - M 5

Metal Stoppers for Pre-Assembly Insertion Square Nuts

HNKKST5

Material: SUS301

Part Number	M	Applicable Pre-Assembly Insertion Nut	Unit Price		
			1 - 9 pkg(s)	10-19	20-30
HNKKST5	3 4 5	HNKK5			

Pre-Assembly Insertion Nuts

Ordering Example: Part Number HNKKST5

Pre-Assembly Insertion Nuts Stainless Steel Sheet Metal Type

HNTTBS5 (SUS304)

Material: SUS304

M	T	D
3	2.7	4.3
4	3.4	5.6
5	3.7	6.7

Ordering Example: Part Number HNTTBS5 - M 5

Post-Assembly Insertion Stopper Nuts

HNTA5 (S10C Equivalent)

PACK-HNTA5 (S10C Equivalent, 100/pkg.)

HNTAV5 (Thread Locking Adhesive Type, S10C Equivalent)

HNTAZ5 (Thread Locking Resin Coating Type, S10C Equivalent)

HNTASN5 (SUS316 Equivalent, Sintered)

PACK-HNTASN5 (SUS316 Equivalent, Sintered, 100/pkg.)

HNTASS5 (SUS303 Equivalent)

Material: S10C Equivalent
Surface Treatment: Trivalent Chromate

Reference Tightening Torque (N·m)
M S10C Equivalent / SUS316 Equivalent (Sintered) / SUS303 Equivalent: 6.8

Part Number	M	Unit Price			
		1 - 499 pc(s)	500-749	750-999	1000-1500
HNTA5 (S10C Equivalent)	3 4				
HNTAV5 (Thread Locking, S10C Equivalent)	5				
HNTAZ5 (Thread Locking, S10C Equivalent)	5				
HNTASN5 (SUS316 Equivalent, Sintered)	3 4 5				
HNTASS5 (SUS303 Equivalent)	5				

Part Number	M	Unit Price (1 - 10 packages)	
		Package Price	Price per Pkg.
PACK-HNTA5 (S10C Equivalent, 100/pkg.)	3 4		
PACK-HNTASN5 (SUS316 Equivalent, Sintered, 100/pkg.)	3 4 5		

Post-Assembly Insertion Stoppers

HNA55 HNB55

Material: Polypropylene (HNA55), SUS301 (HNB55)

Part Number	Applicable Stopper Nut	Color	B	B1	Unit Price		
					1 - 49 pc(s)	50-499	500-999 1000-1500
HNA55	HNTA5 HNTAV5 HNTAZ5 HNTASN5 HNTASS5	White	6.6	5			
HNB55	-	-	8.5	4			

Post-Assembly Insertion Nut and Stopper Set

HNTAT5 (S10C Equivalent Set)

HNTATS5 (SUS316 Equivalent Set)

Type	Stopper Nut	Stopper
HNTAT5	HNTA5	HNA55
HNTATS5*	HNTASN5	HNB55

* Electrically conductive

Part Number	M	Unit Price			
		1 - 499 pc(s)	500-749	750-999	1000-1500
HNTAT5	3 4				
HNTATS5	3 4 5				

Post-Assembly Insertion Nut and Metal Stopper Set

HNTBT5 (S10C Equivalent Set)

HNTBTS5 (SUS316 Equivalent Set)

Type	Stopper Nut	Stopper
HNTBT5	HNTA5	HNA55
HNTBTS5*	HNTASN5	HNB55

* Electrically conductive

Part Number	M	Unit Price			
		1 - 499 pc(s)	500-749	750-999	1000-1500
HNTBT5	3 4				
HNTBTS5	3 4 5				

Ordering Example: Part Number HNTAT5 - M 5

Example: HNTA5, HNTAV5, HNTAZ5, HNTASN5, HNTASS5

* Insert a stopper into the extrusion and put into a nut on it.

* Does not fall even if the extrusion is placed vertically.

Post-Assembly Insertion Nuts

HNTF5 (S10C Equivalent)

HNTFV5 (Thread Locking Adhesive Type, S10C Equivalent)

HNTFZ5 (Thread Locking Resin Coating Type, S10C Equivalent)

HNTFSN5 (SUS316 Equivalent, Sintered)

Material: S10C Equivalent
Surface Treatment: Trivalent Chromate

Reference Tightening Torque (N·m)
M S10C Equivalent / SUS316 Equivalent (Sintered): 6.8

Part Number	M	T	Unit Price			
			1 - 499 pc(s)	500-749	750-999	1000-1500
HNTF5 (S10C Equivalent)	3 4	4.1				
HNTFV5 (Thread Locking, S10C Equivalent)	4	4.1				
HNTFZ5 (Thread Locking, S10C Equivalent)	4	4.1				
HNTFSN5 (SUS316 Equivalent, Sintered)	3 4	5.0				

Post-Assembly Insertion Stopper Nuts

HNTA HNTAV HNTAZ HNTASN HNTASS

Ordering Example: Part Number HNTA5 - M 5

Ordering Example: Part Number HNTA5 - M 5

Post-Assembly Insertion Nut

HNTF HNTFV HNTFZ HNTFSN

Ordering Example: Part Number HNTF5 - M 4

* Post-Assembly Insertion Nuts Stainless Steel Type causes interference with the tab of Tabbed Brackets (P.537, 538, 541) and not usable.

* The 5-5 size Post-assembly Insertion Nuts are not applicable since the outside of tap is thin and thus the tightening force is weak. Use 5-5 size Post-assembly Insertion Nuts and Stopper Set.