



ORDER No.	CUSTOMER
-----------	----------

PRIMARY VOLTAGE (V) 230 (50Hz)



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY		ELECTRIC MOTOR	
CYLINDER DIA.	mm 72	TYPE	EFOUP-KQ
STROKE	mm 65	OUTPUT	2.2 kW 1φ
NO. OF CYLINDER	2	REVOLUTIONS (50Hz)	min ⁻¹ 1430
MAX. PRESS	MPa 0.93	POLES (P)	4
REVOLUTIONS	min ⁻¹ 730	AIR RECEIVER	
CAPACITY	L/min 265	DIAMETER	mm 325
V-BELT (50Hz)	B-63×1	LENGTH	mm 1283
NET WEIGHT	kg 114	CAPACITY	L 90

Painting color: BEBICON Gray

2.2 kW BEBICON		Hitachi Industrial Equipment Systems Co., Ltd.	
2.2P-9.5VS5A			
DRAWN	D. Takahashi	Sep. 20. '06	SCALE
CHECKED	K. Umezawa	Sep. 20. '06	1:12
APPROVED	S. Sakamoto	Sep. 20. '06	
7K-0100~4			