


ORDER No.		CUSTOMER	
-----------	--	----------	--

PRIMARY VOLTAGE (V)	220 (60Hz)	380 (50Hz)	415 (50Hz)
APPLICATION	↑		



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY		ELECTRIC MOTOR	
CYLINDER DIA. mm	60	TYPE	TFO-K
STROKE mm	50	OUTPUT	0.75 kW 3φ
NUMBER OF CYLINDER	1	REVOLUTIONS (50/60Hz) min ⁻¹	1420/1700
MAX. PRESSURE MPa	0.93	POLES (P)	4
REVOLUTIONS min ⁻¹	980	AIR RECEIVER	
CAPACITY L/min	75	DIAMETER mm	325
V-BELT (50/60Hz)	A-56×1/A-54×1	LENGTH mm	1173
NET WEIGHT kg	67	CAPACITY L	80

Painting color: Metaric Green

0.75kW OILFREE BEBICON				Hitachi Industrial Equipment Systems Co.,Ltd.	
0.750P-9.5G5/6A					
DRAWN	D.Takahashi	Sep.10.'06	SCALE	7 K - 7 1 2 5 ~ 2	
CHECKED	K.Umezawa	Sep.10.'06	1:12		
APPROVED	S.Sakamoto	Sep.10.'06			