



ORDER No.	CUSTOMER
-----------	----------

PRIMARY VOLTAGE (V)	220 (60Hz)	380 (50Hz)	415 (50Hz)
APPLICATION	↑		



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY		ELECTRIC MOTOR	
CYLINDER DIA.	mm 72	TYPE	TFO-K
STROKE	mm 65	OUTPUT	2.2 kW 3 φ
NO. OF CYLINDER	2	REVOLUTIONS (50/60Hz) min <sup>-1</sup>	1420 / 1720
MAX. PRESS	MPa 0.93	POLES (P)	4
REVOLUTIONS	min <sup>-1</sup> 730	AIR RECEIVER	
CAPACITY	L/min 265	DIAMETER	mm 375
V-BELT (50/60Hz)	B-63×1/B-61×1	LENGTH	mm 1775
NET WEIGHT	kg 123	CAPACITY	L 170

Painting color: BEBICON Gray

2.2 kW BEBICON		<b>Hitachi Industrial Equipment Systems Co., Ltd.</b>	
2.2P-9.5VL5/6A			
DRAWN	D. Fukushima	May. 14. '09	SCALE
CHECKED	H. Mannen	May. 14. '09	AS SHOWN
APPROVED	M. Sugimoto	May. 14. '09	
8K-0136			