



ORDER No.		CUSTOMER	
-----------	--	----------	--

PRIMARY VOLTAGE (V)	220 (50Hz)	380 (50Hz)	415 (50Hz)
APPLICATION	↑		



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY		ELECTRIC MOTOR		
CYLINDER DIA.	mm	50	TYPE	
STROKE	mm	65	TFO-K	
NO. OF CYLINDER		1	OUTPUT	
MAX. PRESS	MPa	0.93	0.75kW 3φ	
REVOLUTIONS	min <sup>-1</sup>	990	REVOLUTIONS (50Hz)	
CAPACITY	L/min	80	min <sup>-1</sup>	
V-BELT (50Hz)		A-46×1	POLES (P)	
NET WEIGHT	kg	64	4	
			AIR RECEIVER	
			DIAMETER	mm
			325	
			LENGTH	mm
			931	
			CAPACITY	L
			62	

Painting color: BEBICON Gray

0.75kW BEBICON		<b>Hitachi Industrial Equipment Systems Co., Ltd.</b>	
0.75P-9.5V5A			
DRAWN	D. Takahashi	Sep. 20. '06	SCALE
CHECKED	K. Umezawa	Sep. 20. '06	1:12
APPROVED	S. Sakamoto	Sep. 20. '06	
			7K-0097~4