


ORDER No.		CUSTOMER	
-----------	--	----------	--

PRIMARY VOLTAGE (V)	220 (60Hz)	380 (50Hz)	415 (50Hz)
APPLICATION	↑		



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY			ELECTRIC MOTOR	
CYLINDER DIA.	mm	82	TYPE	TFO-K
STROKE	mm	72	OUTPUT	3.7 kW 3φ
NUMBER OF CYLINDER		2	REVOLUTIONS (50/60Hz) min <sup>-1</sup>	1440/1710
MAX. PRESSURE	MPa	0.93	POLES (P)	4
REVOLUTIONS	min <sup>-1</sup>	850	AIR RECEIVER	
CAPACITY	L/min	405	DIAMETER	mm 375
V-BELT (50/60Hz)		3V-750×1/3V-710×1	LENGTH	mm 1345
NET WEIGHT	kg	130	CAPACITY	L 125

Painting color: Metaric Green

3.7kW OILFREE BEBICON 3.70P-9.5G5A 3.70P-9.5G6A				<b>Hitachi Industrial Equipment Systems Co., Ltd.</b>	
DRAWN	N. Narisawa	Apr. 21. '17	SCALE	8K-4981~2	
CHECKED	—	—	N:S		
APPROVED	D. Takahashi	Apr. 21. '17			