



ORDER No.		CUSTOMER	
-----------	--	----------	--

PRIMARY VOLTAGE (V)	380 (50Hz)	415 (50Hz)
APPLICATION	↑	



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY		ELECTRIC MOTOR	
CYLINDER DIA.	mm 72	TYPE	TFO-K
STROKE	mm 65	OUTPUT	2.2 kW 3φ
NO. OF CYLINDER	2	REVOLUTIONS (50Hz) min ⁻¹	1420
MAX. PRESS	MPa 0.93	POLES (P)	4
REVOLUTIONS	min ⁻¹ 730	AIR RECEIVER	
CAPACITY	L/min 265	DIAMETER	mm 325
V-BELT (50Hz)	B-63×1	LENGTH	mm 1283
NET WEIGHT	kg 97	CAPACITY	L 90

Painting color: BEBICON Gray

2.2 kW BEBICON		Hitachi Industrial Equipment Systems Co., Ltd.	
2.2P-9.5V5A			
DRAWN	D. Oka	Sep. 29. '14	SCALE 1:12
CHECKED	H. Manner	Sep. 29. '14	
APPROVED	M. Sugimoto	Sep. 29. '14	
			8 K - 4 9 8 5