



ORDER No.		CUSTOMER	
-----------	--	----------	--

PRIMARY VOLTAGE (V)	380 (50Hz)	415 (50Hz)
APPLICATION	↑	



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY			ELECTRIC MOTOR	
CYLINDER DIA.	mm	82	TYPE	TFO-K
STROKE	mm	60	OUTPUT	2.2 kW 3φ
NUMBER OF CYLINDER		2	REVOLUTIONS (50Hz) min <sup>-1</sup>	1430
MAX. PRESSURE	MPa	0.93	POLES (P)	4
REVOLUTIONS	min <sup>-1</sup>	650	AIR RECEIVER	
CAPACITY	L/min	240	DIAMETER	mm
V-BELT (50Hz)		B-62×1	LENGTH	mm
NET WEIGHT	kg	102	CAPACITY	L

Painting color: Metaric Green

2.2kW OILFREE BEBICON				Hitachi Industrial Equipment Systems Co.,Ltd.	
2.20P-9.5G5A					
DRAWN	D. Oka	Sep. 29. ' 14	SCALE	8 K - 4 9 8 0	
CHECKED	H. Mannen	Sep. 29. ' 14	1:12		
APPROVED	M. Sugimoto	Sep. 29. ' 14			