



ORDER No.	CUSTOMER
-----------	----------

PRIMARY VOLTAGE (V)	380 (50Hz)	415 (50Hz)
APPLICATION	↑	



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY			ELECTRIC MOTOR	
CYLINDER DIA.	mm	(LOW) 90 (HIGH) 50	TYPE	TFO-K
STROKE	mm	85	OUTPUT	3.7 kW 3φ
NO. OF CYLINDER		(LOW) 1 (HIGH) 1	REVOLUTIONS (50Hz) min <sup>-1</sup>	1440
MAX. PRESSURE	MPa	0.93	POLES (P)	4
REVOLUTIONS	min <sup>-1</sup>	1000	AIR RECEIVER	
CAPACITY	L/min	440	DIAMETER	mm 375
V-BELT (50Hz)		3V-710×1	LENGTH	mm 1345
NET WEIGHT	kg	125	CAPACITY	L 125

Painting color: BEBICON Gray

3.7 kW BEBICON				<b>Hitachi Industrial Equipment Systems Co., Ltd.</b>
3.7P-9.5V5A				
DRAWN	H. Mannen	Mar. 3. '15	SCALE	8K-4986~1
CHECKED	-	.	1:12	
APPROVED	M. Sugimoto	Mar. 3. '15		