



ORDER No.		CUSTOMER	
-----------	--	----------	--

PRIMARY VOLTAGE (V)	220 (60Hz)	380 (50Hz)	415 (50Hz)
APPLICATION	↑		



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction (under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY			ELECTRIC MOTOR	
CYLINDER DIA.	mm	(LOW) 105 (HIGH) 60	TYPE	TFO-KK
STROKE	mm	85	OUTPUT	5.5 kW 3φ
NO. OF CYLINDER		(LOW) 1 (HIGH) 1	REVOLUTIONS (50/60Hz) min ⁻¹	1440/1730
MAX. PRESSURE	MPa	0.93	POLES (P)	4
REVOLUTIONS	min ⁻¹	1080	AIR RECEIVER	
CAPACITY	L/min	630	DIAMETER	mm
V-BELT (50/60Hz)		5V-850×1/5V-850×1	LENGTH	mm
NET WEIGHT	kg	186	CAPACITY	L

Painting color: BEBICON Gray

5.5 kW BEBICON				Hitachi Industrial Equipment Systems Co.,Ltd.	
5.5 P-9.5 V5 A					
5.5 P-9.5 V6 A					
DRAWN	M. Yagi	Oct. 31. ' 16	SCALE	8 K - 4 9 8 7 ~ 2	
CHECKED	N. Narisawa	Oct. 31. ' 16	N : S		
APPROVED	D. Takahashi	Oct. 31. ' 16			