



ORDER NO.		CUSTOMER	
-----------	--	----------	--

PRIMARY VOLTAGE (V)	380(50Hz)	415(50Hz)
APPLICATION	↑	



Note)

- 1) Use the compressor at a place where ambient temperature is 0 to 40 degrees C.
- 2) The capacity of compressed air is the amount of air discharged under the maximum pressure converted in terms air suction(under the atmospheric pressure).
- 3) This compressor series is not available for direct use of breathing air.

COMPRESSOR BODY		ELECTRIC MOTOR	
CYLINDER DIA.	mm (LOW)90 (HIGH)72	TYPE	TFO-KK
STROKE	mm 85	OUTPUT	7.5kW 3φ
NO. OF CYLINDER	(LOW)2 (HIGH)1	REVOLUTIONS(50Hz) min ⁻¹	
MAX. PRESSURE	MPa 0.93	POLES(P)	4
REVOLUTIONS	min ⁻¹ 950	AIR RECEIVER	
CAPACITY	L/min 840	DIAMETER	mm 457
V-BELT(50Hz)	5V-950X1	LENGTH	mm 1643
NET WEIGHT	kg 242	CAPACITY	L 230

Painting color : BEBICON Gray

7.5kW BEBICON 7.5P-9.5V5A				Hitachi Industrial Equipment Systems Co.,Ltd.	
DRAWN	S.Maeda	Aug.3.'20	SCALE		
CHECKED	A.Hirata	Aug.3.'20	NOT	8K-4988~2	
APPROVED	M.Sugimoto	Aug.3.'20	SCALE		