


Guides


Straight, L-Shaped, Height Adjusting, Pedestal, Angle

■ **Features:** Each of sizes (in particular, H Dimensions) are downsized for the Compact Type, the newly added lineup. Useful in limited spaces.

■ **Straight Type**



Part Number		Material	Hardness	Surface Treatment
Compact	Standard			
WGHBC	WGHB	S45C Equivalent	40HRC~	Black Oxide
WGHMC	WGHM			Electroless Nickel Plating
-	WGHHB	Aluminum Alloy	-	Black Oxide
-	WGHHM			Electroless Nickel Plating
WGHJC	WGHJ	SUS304	-	-
WGHNC	WGHN	Polyacetal	-	-
-	WGHNE	MC Nylon	-	-
-	WGHPT	Conductive MC Nylon R2	-	-
-	-	PTFE	-	-




RoHS10

Part Number	A Selection	H 1mm Increment	T	h	X	Y	d1	d2	ℓ
(Compact) WGHBC WGHMC WGHJC WGHNC	17 20 20 30	6~10	10 12	H-3	4.5	4.5	6.5	3.5	3.5
(Standard) WGHB WGHM WGHHB WGHJ WGHHM WGHN WGHNE WGHPT	20 30 40 50 20 30 40 50 30 40 50 60 30 40 50 60 40 50 60	10~30	12 15 20 25 30	H-5	5 5 7 8 11	5 6 9 11 14	6.5 8 9.5 11 14	3.5 4.5 5.5 6.5 9	3.5 4.5 5.5 6.5 9


Part Number - A - H - T
WGHJ - 40 - 10 - 20

T	Unit Price												
	Compact				Standard								
	WGHBC	WGHMC	WGHSC	WGHJC	WGHNC	WGHB	WGHM	WGHHB	WGHM	WGHJ	WGHN	WGHNE	WGHPT
10	-	-	-	-	-	-	-	-	-	-	-	-	-
12	-	-	-	-	-	-	-	-	-	-	-	-	-
15	-	-	-	-	-	-	-	-	-	-	-	-	-
20	-	-	-	-	-	-	-	-	-	-	-	-	-
25	-	-	-	-	-	-	-	-	-	-	-	-	-
30	-	-	-	-	-	-	-	-	-	-	-	-	-

■ **L-Shaped Type**



Part Number		Material	Hardness	Surface Treatment
Compact	Standard			
WGLBC	WGLB	S45C Equivalent	40HRC~	Black Oxide
WGLMC	WGLM			Electroless Nickel Plating
-	WGLHB	Aluminum Alloy	-	Black Oxide
-	WGLHM			Electroless Nickel Plating
WGLSC	WGLS	SUS304	-	-
WGLJC	WGLJ	Polyacetal	-	-
WGLNC	WGLN	MC Nylon	-	-
-	WGLNE	Conductive MC Nylon R2	-	-
-	WGLPT	PTFE	-	-




RoHS10

Part Number	A Selection	H 1mm Increment	T	h	X	Y	d1	d2	ℓ
(Compact) WGLBC WGLMC WGLJC WGLNC	17 20 20 30	6~10	10 12	H-3	4.5	4.5	6.5	3.5	3.5
(Standard) WGLB WGLS WGLM WGLJ WGLHB WGLN WGLHM WGLNE WGLA WGLPT	20 30 40 50 20 30 40 50 30 40 50 60 30 40 50 60 40 50 60	10~30	12 15 20 25 30	H-5	5 5 7 8 11	5 6 9 11 14	6.5 8 9.5 11 14	3.5 4.5 5.5 6.5 9	3.5 4.5 5.5 6.5 9


Part Number - A - H - T
WGLMC - 15 - 8 - 10

T	Unit Price														
	Compact				Standard										
	WGLBC	WGLMC	WGLSC	WGLJC	WGLNC	WGLB	WGLM	WGLHB	WGLHM	WGLA	WGLS	WGLJ	WGLN	WGLNE	WGLPT
10	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
12	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
15	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
20	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
25	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

■ **Height Adjusting Type**



Part Number	Material
WGDLJ	Polyacetal
WGDLN	MC Nylon
WGDLNE	Conductive MC Nylon R2




RoHS10


Part Number	A Selection	H 1mm Increment	T 1mm Increment	B	W	F	X	d1	d2	ℓ	b	Unit Price		
												WGDLJ	WGDLN	WGDLNE
WGDLJ WGDLN WGDLNE	15	3~5	2~5	10	10	4	4	4.8	2.4	2.4	7			
	20	3~12	3~10	20	10	5	3.5	6.5	3.5	3.5	15			
	30	3~22		30	15	5	6	8	4.5	4.5	25			
	40	3~32	3~15	40	20	7	9	9.5	5.5	5.5	35			
	50	3~42		50	20	7	9	9.5	5.5	5.5	45			

Part Number - A - H - T
WGDLJ - 20 - 10 - 3

■ **Pedestal Type**




Part Number	Material	Hardness	Surface Treatment
WGDB	S45C Equivalent	40HRC~	Black Oxide
WGDM			Electroless Nickel Plating
WGDHB	Aluminum Alloy	-	Black Oxide
WGDHM			Electroless Nickel Plating
WGDS	SUS304	-	-
WGDJ	Polyacetal	-	-
WGDN	MC Nylon	-	-
WGDNE	Conductive MC Nylon R2	-	-




RoHS10

Part Number	A Selection	H 1mm Increment	T 1mm Increment	B	W	X	Y	d1	d2	ℓ	Unit Price						
											WGDB	WGDM	WGDHB	WGDHM	WGDS	WGDJ	WGDN
WGDB WGDM WGDHB WGDHM WGDS WGDJ WGDN WGDNE	20	3~12	2~15	20	15	5	6	8	4.5	4.5							
	30			30	20	7	9	9.5	5.5	5.5							
	40	5~20		40	20	7	9	9.5	5.5	5.5							
	50			50	25	8	11	11	6.5	6.5							
	60	10~25		60	25	8	11	11	6.5	6.5							


Ordering Example Part Number - A - H - T
WGDM - 30 - 10 - 10



■ **Angle Type**



Part Number	Material	Hardness	Surface Treatment
WGNB	S45C Equivalent	40HRC~	Black Oxide
WGNM			Electroless Nickel Plating
WGNHB	Aluminum Alloy	-	Black Oxide
WGNHM			Electroless Nickel Plating
WGNA	SUS304	-	-
WGNJ	Polyacetal	-	-
WGNL	MC Nylon	-	-
WGNNE	Conductive MC Nylon R2	-	-



RoHS10

Part Number Type	A Selection	H 10mm Increment	T	h	B	F	S	W	K	Unit Price							
										WGNB	WGNM	WGNHB	WGNHM	WGNA	WGNL	WGNJ	WGNL
WGNB WGNM WGNHB WGNHM WGNA WGNL WGNJ WGNL WGNNE	20	20~60	8	H-5	30	11	19	3.5	8								
	30		10		40	16	25	4.5	10								
	40		10		40	26	25	4.5	10								
	50		12		50	32	31	5.5	15								
	60		12		50	42	31	5.5	15								

Ordering Example Part Number - A - H
WGNJ - 20 - 40