

Sanitary Pipe Fittings

Both Ends Weld-On

Sanitary Pipe Fittings / Sanitary Adapter Fittings

Weld-On Threaded

Both Ends Weld-On, Elbows

Type	Material
SNWE	SUS304
SNWES	SUS316L

RoHS10

Both Ends Weld-On, 45° Elbows

Type	Material
SNWHE	SUS304
SNWHES	SUS316L

RoHS10

Both Ends Weld-On, Tees

Type	Material
SNWT	SUS304
SNWTS	SUS316L

RoHS10

Both Ends Weld-On, Reducing Tees

Type	Material
SNWTD	SUS304

RoHS10

Blind Nuts

Type	Material
SNYBN	SUS304

RoHS10

Part Number		D	d	L	SNWE		SNWES	
Type	No.				Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SNWES	8A	13.8	10.5	38	-	-	-	-
	10A	17.3	14.0		-	-	-	-
	15A	21.7	17.5		-	-	-	-
SNWE	1S	25.4	23	34	-	-	-	-
	1.5S	38.1	35.7	49	-	-	-	-
	2S	50.8	47.8	61	-	-	-	-
	2.5S	63.5	59.5	84	-	-	-	-
	3S	76.3	72.3	89	-	-	-	-

For orders larger than indicated quantity, please check with WOS.

Part Number		D	d	L	SNWHE		SNWHES	
Type	No.				Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SNWHE	1S	25.4	23	15.8	-	-	-	-
	1.5S	38.1	35.7	23.7	-	-	-	-
	2S	50.8	47.8	31.6	-	-	-	-
	2.5S	63.5	59.5	42	-	-	-	-
	3S	76.3	72.3	52.6	-	-	-	-

For orders larger than indicated quantity, please check with WOS.

Part Number		D	d	L	SNWT		SNWTS	
Type	No.				Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SNWT	1S	25.4	23.0	34.0	-	-	-	-
	1.5S	38.1	35.7	49.0	-	-	-	-
	2S	50.8	47.8	61.0	-	-	-	-
	2.5S	63.5	59.5	84.0	-	-	-	-
3S	76.3	72.3	89.0	-	-	-	-	

For orders larger than indicated quantity, please check with WOS.

Part Number		D1	d1	D2	d2	L1	L2	Unit Price
Type	No.							Qty. 1 ~ 10
SNWTD	1.5S-1S	38.1	35.7	25.4	23.0	49	45	-
	2S-1S	50.8	47.8	25.4	23.0	61	51	-
	2S-1.5S	50.8	47.8	38.1	35.7	61	64	-
	2.5S-1.5S	63.5	59.5	38.1	35.7	84	70	-
2.5S-2S	63.5	59.5	50.8	47.8	84	82	-	

For orders larger than indicated quantity, please check with WOS.

Part Number		A	B	(T)	Unit Price	Volume Discount Rate
Type	No.				Qty. 1 ~ 4	5~10
SNYBN	1S	46.0	53.1	30.0	-	-
	1.5S	56.0	64.6		-	-
	2S	71.0	81.9		-	-
	2.5S	85.0	98.1		-	-
	3S	100.0	115.4		-	-

For orders larger than indicated quantity, please check with WOS.

Weld-On Threaded Seats

Type	Material
SNYNS	SUS304

RoHS10

Weld-On Liners

Type	Material
SNYRN	SUS304

RoHS10

Hex Nuts

Type	Material
SNRN	SUS304

RoHS10

L-Shaped Gaskets

Type	Material
SNLGS	Silicone
SNLGSF	PTFE

RoHS10

Male Threads Type

Type	Material
SNWZFA	SUS316L

RoHS10

Hose Type

Type	Material
SNWHAD	SUS304

RoHS10

Part Number		D	d	Unit Price	Volume Discount Rate
Type	No.			Qty. 1 ~ 9	10~20
SNYNS	1S	25.4	23.0	-	-
	1.5S	38.1	35.7	-	-
	2S	50.8	47.8	-	-
	2.5S	63.5	59.5	-	-
	3S	76.3	72.3	-	-

For orders larger than indicated quantity, please check with WOS.

Part Number		D	d	Unit Price	Volume Discount Rate
Type	No.			Qty. 1 ~ 9	10~20
SNYRN	1S	25.4	23.0	-	-
	1.5S	38.1	35.7	-	-
	2S	50.8	47.8	-	-
	2.5S	63.5	59.5	-	-
	3S	76.3	72.3	-	-

For orders larger than indicated quantity, please check with WOS.

Part Number		A	(B)	Unit Price	Volume Discount Rate
Type	No.			Qty. 1 ~ 9	10~20
SNRN	1S	46	53.1	-	-
	1.5S	56	64.6	-	-
	2S	71	81.9	-	-
	2.5S	85	98.1	-	-
	3S	100	115.4	-	-

For orders larger than indicated quantity, please check with WOS.

Part Number		A	SNLGS		SNLGSF	
Type	No.		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SNLGS SNLGSF	1S	32.5	33.4	-	-	-
	1.5S	46.0	46.8	-	-	-
	2S	59.5	60.5	-	-	-
	2.5S	73.2	74.0	-	-	-
	3S	86.5	87.0	-	-	-

Use Weld-On Threaded Seats (SNYNS) with gaskets. For orders larger than indicated quantity, please check with WOS.

Ordering Example: Part Number SNYNS1S

Example: Weld-On Liner, Weld-On Threaded Seat, Hex Nut, L-Shaped Gasket

Part Number		Nominal	R (PT)	A	B	C	D	L1	L2	Unit Price	Volume Discount Rate
Type	No.									Qty. 1 ~ 4	5~10
SNWZFA	1S	4	1/2	21.7	15.7	25.4	23	39	7	-	-
		6	3/4	27.2	21	25.4	23	39	7	-	-
		8	1	34	26	25.4	23	39	7	-	-
		10	1 1/4	42.7	35.7	38.1	35.7	44	7	-	-
	1.5S	8	1	34	26	38.1	35.7	39	7	-	-
		10	1 1/4	42.7	35.7	38.1	35.7	44	7	-	-
		12	1 1/2	48.6	40	50.8	47.8	49	-	-	-
		-	-	-	-	-	-	-	-	-	-

For orders larger than indicated quantity, please check with WOS.

Part Number		D	L	Unit Price	Volume Discount Rate
Type	No.			Qty. 1 ~ 9	10~14
SNWHAD	1S	25.4	60	-	-
	1.5S	38.1	80	-	-
	2S	50.8	80	-	-
	2.5S	63.5	80	-	-
	3S	76.3	80	-	-

For orders larger than indicated quantity, please check with WOS.

Ordering Example: Part Number SNWE2S

Example

Example: Weld-On Liner, Weld-On Threaded Seat, Hex Nut, L-Shaped Gasket

Ordering Example: Part Number SNWTD2S-1.5S - Nominal SNWZFA1S - 6