

SUCTION BRACKET

—SCREW MOUNTING / CYLINDER MOUNTING TYPE—

SUCTION BRACKET / SET SCREW

—SMALL DIAMETER SCREW MOUNTING TYPE—

VC-KNG (Screw mounting type)

Accessory (included)

Type	Parts	Material	Surface treatment
VC-KNG	① Body	A6061	White alumite
	② Spring	Carbon steel	-
	③ Fitting / Stop plug	SUM22 equivalent	Electroless nickel plated

VC-KNGS (Small diameter screw mounting type)

Small diameter set screw

Small Diameter Set Screw
Allen side 5

Type	Material
VC-KNGS	SUS303 equivalent

Applicable cup	Applicable tube Outer×Inner	Weight (g) ^{*1}	L	E	F	J	K	Q	H	d	C	T	Included fitting	Part Number		Stroke	Unit price
														Type	D		
VC-SP	6×4	8	41	5		2.5	5	13	12	5	8.5	2.5	Pipe fitting: 1 pc (Applicable tube) 4×2.5	VC-KNG	7	5	Quotation
		9	46												10		
		10	56												20		
		11	66												30		
		8	44												5		
VC-HSP	6×4	9	49	8		4.2	8	16	12	5	8.5	2.5	Pipe fitting: 1 pc (Applicable tube) 4×2.5	VC-KNG	11	5	Quotation
		10	59												10		
		11	69												20		
		10	59												30		
		11	69												30		

Order **Part Number** — **ST**
VC-KNG11 — ST20

Days to Ship
Quotation

Applicable cup	Applicable tube Outer×Inner	Weight (g) ^{*1}	L	E	F	H	d	C	T	M×P	Q	Part Number		Stroke	Unit price
												Type	D		
VC-HSP3	4×2.5	6	35	4	9	5	3	5	3	M3×0.5	7	VC-KNGS	2.5	5	Quotation

Order **Part Number** — **ST**
VC-KNGS2.5 — ST5

Days to Ship
Quotation

^{*1} The weight is an approximate value. Consider it a guideline. Please check with our WOS for the purchase order that exceeds the displayed quantity.
 Set screw (VC-TNS2.5) is attached to the tip of the suction bracket.

^{*1} The weight is an approximate value. Consider it a guideline. Please check with our WOS for the purchase order that exceeds the displayed quantity.
 A φ 5 fitting (connected to tube outer diameter 6×4) is attached to the suction bracket body. A φ 3.6 fitting is also included as an accessory, enabling switching according to the specifications.

VC-KNGB (Cylinder mounting type)

Accessory (included)

Type	Parts	Material	Surface treatment
VC-KNGB	① Body	A6061	White alumite
	② Spring	Carbon steel	-
	③ Fitting / Stop plug	SUM22 equivalent	Electroless nickel plated

VC-TNS2.5 (Small diameter set screw)

Type	Material
VC-TNS2.5	SUS303 equivalent

Part Number	Unit price	Order	Part Number	Days to Ship	Quotation
Type	1~10 pcs		VC-TNS2.5		Quotation
VC-TNS2.5	Quotation				

^{*1} The weight is an approximate value. Consider it a guideline. Please check with our WOS for the purchase order that exceeds the displayed quantity.

Applicable cup	Applicable tube Outer×Inner	Weight (g) ^{*1}	L	E	F	J	K	Q	H	d	C	T	P	Included fitting	Part Number			Unit price
															Type	D1	ST	
VC-SP	6×4	17.5	49	5		2.5	5	13	12	5	8.5	2.5	20	For piping Fitting: 1 pc (Applicable tube) 4×2.5	VC-KNGB	7	5	Quotation
		18.0	54													10		
		19.0	64													20		
		19.5	74													30		
		18.5	52													5		
VC-HSP	6×4	18.5	57	8		4.2	8	16	12	5	8.5	2.5	20	For piping Fitting: 1 pc (Applicable tube) 4×2.5	VC-KNGB	11	5	Quotation
		19.5	67													10		
		20.5	77													20		
		19.5	67													30		
		20.5	77													30		

Order **Part Number** — **ST** — **D2**
VC-KNGB7 — ST10 — D15

Days to Ship
Quotation

ex Example

Attach and fix the thread of the suction bracket to the screw hole of the slide bracket (FP-SLBCM).

Attach and fix the cylindrical part of the suction bracket to the pipe holder (AT-PHC).