


NEW

GRIP

— PARALLEL GRIP / THREE-JAW GRIP —


REMOVAL RELATED PRODUCTS

Parallel Grip



M Material	S Surface treatment
Aluminum product	Anodizing

MGMHZ



- ① Single action: Ventilation is required when the product is gripped. No ventilation is required when the product is released.
- ② Double action: Ventilation is required when the product is either gripped or released.
- ③ This product's function is a pick-and-place component and is used for the installation of Grip fixtures.
- Note that it may not be compatible to assemble with other products.
- ④ When tightening, the gap is controlled to be less than 1mm.
- ⑤ The surface is anodized, and the color of the actual product may vary from the product picture.

Air pressure range (MPa)	Cylinder bore	
	10	16/20
Double action	0.2~0.7	0.1~0.7
Single action	0.35~0.7	0.25~0.7

Part Number			A	AA	AB	B	C	D	E	F	G	H	I	J	K	K1	K3	M	N
Type	Cylinder bore	Mode of action																	
MGMHZ	10	S (Single action)	6	18	12	23	12	37.8	57	29	15.2	11.2	4	16	M3×0.5	6	6	27	φ 11H9 Depth 2
	16		D (Double action)	7.5	22	15	24.5	15	42.5	67.3	38	20.9	14.9	5	24	M4×0.7	4.5	8	30
	20	D (Double action)	9.5	32	18	29	20	52.8	84.8	50	26.3	16.3	8	30	M5×0.8	8	10	35	φ 21H9 Depth 3

Cylinder bore	O	P	Q	R	S	T	U	V	W	X	Y	Y1	Y2	Z
10	11.4	M2.5×0.45	3	5.7	M3×0.5	23	9	19	5	11	φ 2H9 Depth 3	5.2-0.02	7.6-0.02	16.4-0.05
16	16	M3×0.5	4	7	M5×0.8	30.6	7.5	19	8	13	φ 3H9 Depth 3	6.5-0.02	11-0.02	23.6-0.05
20	18.6	M4×0.7	5	9	M5×0.8	42	10	23	10	15	φ 4H9 Depth 4	7.5-0.02	16.8-0.02	27.6-0.05



Order

Part Number
MGMHZ10S



Days to Ship

Quotation



Price


Quotation

Three-jaw Grip



M Material	S Surface treatment
Aluminum product	Anodizing

MHS



- ① Double action: Ventilation is required when the product is either gripped or released.
- ② This product's function is a pick-and-place component and is used for the installation of Grip fixtures.
- Note that it may not be compatible to assemble with other products.
- ③ When tightening with steel tubes, the gap is controlled to be less than 1mm.
- ④ The surface is anodized, and the color of the actual product may vary from the product picture.

Three-jaw grip:
Air pressure range (MPa):0.2~0.6

Part Number			AA	AB	B	CB	EC	EO	FX	FY	G	I	J	K	NA	NB	O	P	Q	SC	TB	UB	WA		
Type	Cylinder bore	Mode of action																							
MHS	16	D (Double action)	35	32	30	11	5	7	12.5	11	25	4	10	4	8	5h9	2	M3×0.5	6	8	5	4.5	17H9		
	20		38	35	36	13	6	8	14.5	13	27	5	12	5	10	6h9	2.5	M5×0.8	7	9.5	6	6	21H9		



Order

Part Number
MHS16D



Days to Ship

Quotation



Price

Quotation