


Leveling Mount

Standard



NFJN
NFJNS
NFJNF
(Stainless Steel)



M (Coarse)
ℓ₂
A
ℓ₁
E
B
t

M	D	ℓ ₁	ℓ ₂	E	B	t
5	30	3.5	4	5.4	8	1.6
6		4	5		10	
8	38	5.5	6.5	11	13	
10		7	8		17	
12	60	8	10	18	19	
16	75	10	13	20	24	2.0
20		13	16		30	

Type	M Material	S Surface Treatment
NFJN	SS400	Trivalent Chromate
NFJNF	Equivalent	Trivalent Chromate
NFJNS	SUS304	Electrolytic Polishing

RoHS

⚙️ Screw shafts can turn independently of a base and can tilt 3 to 5 degrees.

A Selectable

Part Number	M-A	L	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
					NFJN	NFJNS
NFJN (Stainless Steel) NFJNS	5 - 30	40.5	1.5	15		
	5 - 60	70.5		19		
	6 - 40	51	2.1	21		
	6 - 80	91		28		
	8 - 50	68.1	3.9	50		
	8 -100	118.1		65		
	10 - 75	94.6	4.3	88		
	10 -100	119.6		100		
	12 - 50	78	4.9	142		-
	12 - 75	103		166		
	12 -100	128		184		
	12 -125	153		200		
	12 -150	178	5.9	219		
	16 - 75	107		287		
	16 -100	132		317		
	16 -130	162		356		
	16 -150	182	8.8	383		
	16 -180	212		422		
	20 -100	135		493		
	20 -130	163		557		
	20 -150	183		605		
	20 -180	213		671		

A configurable in 10mm Increment

Part Number	M	A 10mm Increment	L	Unit Price
NFJNF	10	80~200	A+19.6	
	12	80~250	A+28	
	16	80~300	A+32	
	20	110~300	A+35	

⚙️ Tips of screws are painted.







Ordering Example
Part Number - A
NFJN12-100 - 80
NFJNF10 - 80



Alterations
Part Number - (WC, WK, SC, WN)
NFJN16-75 - WC

⚙️ For NFJN only. ⚙️ No plating on alteration-applied sections. ⚙️ For alterations for 31 or more pieces, please request a quotation.


Alterations	Square Flats	Hex Flats	Wrench Flats	Hex Wrench Socket Machining
	 WC ℓ	 WK ℓ	 W SC ℓ ₁	 WN ℓ
Code	WC	WK	SC	WN
Spec.	Ordering Code WC ⚙️ Applicable when 20≥M≥10	Ordering Code WK ⚙️ Applicable when 20≥M≥10	Ordering Code SC ⚙️ Applicable when 20≥M≥10	Ordering Code WN ⚙️ Applicable when 20≥M≥10
	M WC ℓ 10 6 10 12 8 10 16 10 12 20 12 13.5	M WK ℓ 10 6 10 12 8 10 16 10 12 20 13 13	M W ℓ ₁ SC 10 8 8 20 12 10 10 20 16 13 10 20 20 17 10 20	M WN ℓ 10 4 5 12 5 6 16 8 8 20 8 8

Leveling Mount

Non-Slip



RoHS



② Rubber (Capped)
① Main Body
M (Coarse)
ℓ₂
A
ℓ₁
E
B
H

Main Body	Type	① Main Body M Material S Surface Treatment	② Rubber M Material (Color) H Hardness
Steel Type	FJGN	SS400 Equivalent	Trivalent Chromate
	FJGM		
Stainless Steel	FJGNS	SUS304	Electrolytic Polishing
	FJGMS		

M	D	ℓ ₁	ℓ ₂	E	B	H
8	45	5.5	6.5	15	13	6
10		7	8		17	6
12	70	8	10	23	19	7
16	80	10	13	25	24	8
20		13	16		30	

⚙️ Electrically Conductive Rubber Specific Volume Resistivity 10² ~ 10⁴Ω·cm
⚙️ Screw shaft turns independently of the base and tilts slightly.

Part Number		FJGM / FJGMS	L	Allowable Vertical Load (kN)	Mass (g)	Unit Price								
Type	M-A	Rubber Material				FJGN	FJGM				FJGNS	FJGMS		
							R	C	D	S		R	C	D
FJGN FJGM FJGNS (Stainless Steel) FJGMS (Stainless Steel)	8- 50	R (Rubber) C (Non-migration Chloroprene Rubber) D (Electrically Conductive Rubber) S (PVC)	70.5	3.9	50					-				
	8-100		120.5		70					-				
	10- 75		97	4.3	91					-				
	10-100		122		103					-				
	12- 75		106	4.9	178					-				
	12-100*		131		196									
	12-125*		156		212									
	12-150		181		231					-				
	16- 75		110	5.9	301					-				
	16-100*		135		331									
	16-130*		165		370									
	16-150		185		397					-				
	16-180*		215	6.8	436									
	20-100*		138		148		-	-	-		-	-	-	-
	20-130*		168		173		-	-	-		-	-	-	-
	20-150		188		194		-	-	-		-	-	-	-
	20-180*		218		220		-	-	-		-	-	-	-

⚙️ You cannot select the rubber material for FJGN and FJGNS. (Elastomer is used.) * PVC rubber applicable sizes



Ordering Example
Part Number - Rubber Material
FJGM16 - 75 - R