


ミスミ

TiN COATED HSS DRILLS

TiNコートハイス鋼ドリル

●テーパシャンク/レギュラー -TAPERSHANK/REGULAR LENGTH-

G-TD



S形シンニング



| 材質 | | | <table border="1"> <tr> <th>直径D</th> <th>公差 (h8)</th> </tr> <tr> <td>10.5~18</td> <td>0 -0.027</td> </tr> <tr> <td>18.5~30</td> <td>0 -0.033</td> </tr> </table> | | 直径D | 公差 (h8) | 10.5~18 | 0 -0.027 | 18.5~30 | 0 -0.033 |
|-----------------------|-----------------------|--------------|--|----------------|--------------|-----------------------|-----------------------|-------------|---------|-------------|
| 直径D | 公差 (h8) | | | | | | | | | |
| 10.5~18 | 0 -0.027 | | | | | | | | | |
| 18.5~30 | 0 -0.033 | | | | | | | | | |
| 仕様 | | | | | | | | | | |
| 一般鋼 (SS-SC材) | 合金鋼 (SCM) | 調質鋼 (~45HRC) | 高硬度鋼 (50HRC~) | 工具鋼 (SKD, SKS) | ステンレス鋼 (SUS) | 鋳鉄 (FC, FCD) | アルミ (Al) | 銅 (Cu) | | |
| <input type="radio"/> | <input type="radio"/> | | | | | <input type="radio"/> | <input type="radio"/> | | | |

○=適

型番 **G-TD** 1本単位

| 直径 D | 溝長 l | 全長 L | MT No. | ¥通常単価 10本以上お見積り | | |
|------|------|------|--------|-----------------|--------|--------|
| | | | | 1本 | 2~4本 | 5~9本 |
| 10.5 | 87 | 168 | 1 | 4,220 | 4,090 | 4,000 |
| 12.5 | 101 | 182 | 1 | 5,110 | 4,950 | 4,850 |
| 13.5 | 108 | 189 | 1 | 5,640 | 5,470 | 5,350 |
| 14 | 108 | 189 | 1 | 6,010 | 5,820 | 5,700 |
| 14.5 | 114 | 212 | 2 | 6,550 | 6,350 | 6,220 |
| 15 | 114 | 212 | 2 | 6,550 | 6,350 | 6,220 |
| 15.5 | 120 | 218 | 2 | 7,060 | 6,840 | 6,700 |
| 16 | 120 | 218 | 2 | 7,060 | 6,840 | 6,700 |
| 16.5 | 125 | 223 | 2 | 7,310 | 7,090 | 6,940 |
| 17 | 130 | 228 | 2 | 7,310 | 7,090 | 6,940 |
| 17.5 | 130 | 228 | 2 | 8,190 | 7,940 | 7,780 |
| 18 | 130 | 228 | 2 | 8,190 | 7,940 | 7,780 |
| 18.5 | 135 | 233 | 2 | 8,630 | 8,370 | 8,190 |
| 19 | 135 | 233 | 2 | 8,630 | 8,370 | 8,190 |
| 19.5 | 140 | 238 | 2 | 9,260 | 8,980 | 8,790 |
| 20 | 140 | 238 | 2 | 9,260 | 8,980 | 8,790 |
| 20.5 | 145 | 243 | 2 | 10,840 | 10,510 | 10,290 |
| 21 | 145 | 243 | 2 | 10,840 | 10,510 | 10,290 |
| 21.5 | 150 | 248 | 2 | 11,850 | 11,490 | 11,250 |
| 22.5 | 155 | 253 | 2 | 12,610 | 12,230 | 11,970 |
| 24 | 160 | 281 | 3 | 14,690 | 14,240 | 13,950 |
| 25 | 160 | 281 | 3 | 15,690 | 15,210 | 14,900 |
| 27 | 170 | 291 | 3 | 18,090 | 17,540 | 17,180 |
| 30 | 175 | 296 | 3 | 22,630 | 21,950 | 21,490 |



Order 注文例

G-TD 20

型番 直径 (D)

切削条件 P.766



Delivery 出荷日



在庫品

巻末-3

🔴 ご希望によりPM6:00迄、当日出荷受付致します。