

Phillips Pan Head Screws with Captured Washer


Single Item Sale

Phillips Pan Head Screws with Captured Washer SW+JIS W Captured



RoHS10

NSET SCBJ



NSET

Screw	M	Material: SWCH Equivalent
Washers	Spring Washer	JIS B 1251
	Flat Washer	JIS B 1256
Surface Treatment	Trivalent Chromate	

SCBJ

Screw	M	Material: SUS304 Equivalent
Washers	Spring Washer	JIS B 1251
	Flat Washer	JIS B 1256


MxP	A	E	C (Max.)	D	(a)	Phillips No.
2 x0.4	3.5	1.3	4.0	6.0	2.1	1
2.5x0.45	4.5	1.7	4.8	6.5	2.7	1
2.6x0.45	4.5	1.7	4.8	7.5	2.7	1
3 x0.5	5.5	2.0	5.5	8.0	3.0	2
4 x0.7	7.0	2.6	7.0	10.0	4.4	2
5 x0.8	9.0	3.3	8.5	12.0	5.4	2
6 x1.0	10.5	3.9	11.5	13.0	6.9	3

Phillips Pan Head Screws with Captured Washer SW+JIS Compact W Captured



RoHS10

PSET PSETS



PSET

Screw	M	Material: SWCH Equivalent
Washers	Spring Washer	JIS B 1251
	Flat Washer	JIS B 1256
Surface Treatment	Trivalent Chromate	

PSETS

Screw	M	Material: SUS304 Equivalent
Washers	Spring Washer	JIS B 1251
	Flat Washer	JIS B 1256

MxP	A	E	C (Max.)	D	(a)	Phillips No.
3x0.5	5.5	2.0	5.5	6.0	3.0	2
4x0.7	7.0	2.6	7.0	8.0	4.4	2
5x0.8	9.0	3.3	8.5	10.0	5.4	2
6x1.0	10.5	3.9	11.5	11.5	6.9	3

Part Number		NSET		SCBJ			
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate		
Type	M-L	1 ~ 99 pc(s).	100 ~ 500 pcs.	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150 ~ 500 pcs.
NSET SCBJ	2 - 4						
	5						
	6						
	8						
	10						
	12						
	14						
	15						
	16						
	20						
NSET SCBJ	2.5 - 4						
	5						
	6						
	8						
	10						
	12						
	14						
	15						
	16						
	20						
NSET SCBJ	2.6 - 4						
	5						
	6						
	8						
	10						
	12						
	14						
	15						
	16						
	20						
NSET SCBJ	3 - 5						
	6						
	8						
	10						
	12						
	14						
	15						
	16						
	20						
	25						
NSET SCBJ	4 - 5						
	6						
	8						
	10						
	12						
	14						
	16						
	20						
	25						
	30						
NSET SCBJ	5 - 8						
	10						
	12						
	14						
	16						
	20						
	25						
	30						
	35						
	40						
NSET SCBJ	6 - 10						
	12						
	14						
	16						
	20						
	25						
	30						
	35						
	40						
	45						


Part Number		PSET		PSETS			
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate		
Type	M-L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 149 pcs.	150 ~ 500 pcs.	1 ~ 29 pc(s).	30 ~ 99 pcs.
PSET PSETS	3 - 6						
	8						
	10						
	12						
	15						
	4 - 6						
	8						
	10						
	12						
	15						
PSET PSETS	5 - 8						
	10						
	12						
	15						
	6 - 10						
	12						
	15						
	20						
	25						
	30						

Phillips Pan Head Screws with Captured Washer SW Captured



RoHS10

WSET WSETS



WSET

Screw	M	Material: SWCH Equivalent
Washers	Spring Washer	JIS B 1251
	Flat Washer	JIS B 1256
Surface Treatment	Trivalent Chromate	

WSETS

Screw	M	Material: SUS304 Equivalent
Washers	Spring Washer	JIS B 1251
	Flat Washer	JIS B 1256


MxP	A	E	C (Max.)	(a)	Phillips No.
3x0.5	5.5	2.0	5.5	2.4	2
4x0.7	7.0	2.6	7.0	3.5	2
5x0.8	9.0	3.3	8.5	4.3	2
6x1.0	10.5	3.9	11.5	5.1	3

Phillips Hex Head Screws with Captured Washer



RoHS10

BSET SBSET (Stainless Steel)



BSET

Screw	M	Material: Structural Alloy Steel Screw: JIS 0209 (6g)
Washers	Spring Washer	JIS B1251
	Flat Washer	JIS B1256
Surface Treatment	Trivalent Chromate	

SBSET

Screw	M	Material: SUS304 Equivalent *Strength Class A2-50 Equivalent Screw: JIS 0209 (6g)
Washers	Spring Washer	JIS B1251
	Flat Washer	JIS B1256
Surface Treatment	Barrel, Passivated	

MxP	A	E	C	D	(a)
4x0.7	7	2.8	7.0	10	4.4
5x0.8	8	3.5	8.5	12	5.2
6x1.0	10	4.0	11.5	13	6.3
8x1.25	13	5.5	14.5	18	8.4

(a) is the max length (reference) between head surface and the complete thread.



Ordering
Example

Part Number
WSET5-10
BSET4-8

Part Number		WSET				WSETS			
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
Type	M-L	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 199 pcs.	200 ~ 500 pcs.	1 ~ 29 pc(s).	30 ~ 99 pcs.	100 ~ 199 pcs.	200 ~ 500 pcs.
WSET WSETS	3 - 6								
	8								
	10								
	12								
	4 - 8								
	10								
	12								
	15								
	5 - 8								
	10								
WSET WSETS	12								
	15								
	6 - 10								
	12								
	15								
	20								
	25								
	30								
	35								
	40								

Part Number		BSET		SBSET		Part Number		BSET		SBSET	
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate			Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
Type	M-L	1 ~ 99 pc(s)	100 ~ 500 pcs.	1 ~ 99 pc(s)	100 ~ 500 pcs.	Type	M-L	1 ~ 99 pc(s)	100 ~ 500 pcs.	1 ~ 99 pc(s)	100 ~ 500 pcs.
BSET SBSET	4- 8					BSET SBSET	6-20				
	10						25				
	12						30				
	14						35			-	-
	16						40			-	-
	20						45			-	-
	25			-	-		50			-	-
	30			-	-		55			-	-
	35			-	-		60			-	-
	40			-	-		65			-	-
45			-	-	70			-	-		
50			-	-	75			-	-		
BSET SBSET	5-10					BSET SBSET	8-12				
	12						14				
	14						16				
	20						20				
	25						25				
	30						30				
	35			-	-		35			-	-
	40			-	-		40			-	-
	45			-	-		45			-	-
	50			-	-		50			-	-
BSET SBSET	6-10					55			-	-	
	12					60			-	-	
	14					65			-	-	
	16					70			-	-	
					75			-	-		