




RoHS: Not Compliant, Standard for Running Test: Internal Standard Based on GB (for details, see P.1063)

Similar Products Page P.1066


Swivel



View X

Part Number Type	D	Wheel Material	H	A	C	F ₁	F ₂	G ₁	G ₂	d	B	E	r	Allowable Load (N)	Mass (g)	Unit Price
C-CTCJ	75	R (Rubber)	97	84	72	64.3	59.3	54	50	8.5	25	32.5	70	700	485	
	100		128	105	85	82.5	70	62.5	50	9	30	38.5	90	1000	900	
	125		153													
	150		187	135	105	110	100	85	75	10	40	68.5	143	1600	2350	


Fixed



View X

Part Number Type	D	Wheel Material	H	A	C	F ₁	F ₂	G ₁	G ₂	d	B	Allowable Load (N)	Mass (g)	Unit Price
C-CTCK	75	R (Rubber)	97	84	72	64.3	59.3	54	50	8.5	25	700	399	
	100		128	105	85	82.5	70	62.5	50	9	30	1000	714	
	125		153											
	150		187	140	110	110	100	85	75	10	40	1600	1865	

Swivel with Stopper



View X

Part Number Type	D	Wheel Material	H	A	C	F ₁	F ₂	G ₁	G ₂	d	B	E	r	Allowable Load (N)	Mass (g)	Unit Price
C-CTCS	75	R (Rubber)	97	84	72	64.3	59.3	54	50	8.5	25	32.5	93	700	563	
	100		128	105	85	82.5	70	62.5	50	9	30	39.5	125	1000	1120	
	125		153													
	150		187	135	105	110	100	85	75	10	40	68.5	184	1600	2524	




Ordering Example
Part Number - Wheel Material
C-CTCJ75 - R



RoHS: Not Compliant, Standard for Running Test: Internal Standard Based on GB (for details, see P.1063)

Similar Products Page P.1066


Swivel



View X

Part Number Type	D	Wheel Material	H	B	E	r	Allowable Load (N)	Mass (g)	Unit Price
C-CTFJ	80	P (Polypropylene)	106	35	37.5	77.5	600	608	
	100		128		40	90	700	727	
	125		153		47	109.5	900	861	

Swivel with Stopper



View X

Part Number Type	D	Wheel Material	H	B	E	r	Allowable Load (N)	Mass (g)	Unit Price
C-CTFS	80	P (Polypropylene)	106	35	37.5	125	600	770	
	100		128		40	125	700	828	
	125		153		47	127	900	976	



Ordering Example
Part Number - Wheel Material
C-CTFJ80 - P