


Leveling Mounts - Space Saving

Leveling Mounts

Pivot Type / Tapped Socket Type

Foot (D dimension) is more compact than that of the conventional leveling mounts.





RoHS


Screw shafts turn.

M Material: SS400 Equivalent
S Surface Treatment: Trivalent Chromate

Part Number		M (Coarse)	A			H	ℓ1	ℓ2	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
Type	D											LEMNT	LEMNS
HNFJN	28	8	20	50	100	17.7	5.2	6.5	13	6.5	48		
	38	12	30	80	100	23	7.4	10	19	13	55		
	48	8	20	50	100	20.7	5.2	6.5	13	6.5	77		
		12	30	80	100	23	7.4	10	19	13	90		
	58	8	20	50	100	20.7	5.2	6.5	13	6.5	121		
		12	30	80	100	23	7.4	10	19	13	133		

Pivot Type





RoHS

Screw shafts turn.

M Material: SS400 Equivalent
S Surface Treatment: Trivalent Chromate


Part Number		M (Coarse)	A			H	ℓ1	ℓ2	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
Type	D											LEMNT	LEMNS
HNFJR	28	8	20	50	100	28.2	5.2	6.5	13	6.5	50		
	38	12	30	80	100	35.4	7.4	10	19	13	59		
	48	8	20	50	100	33.2	5.2	6.5	13	6.5	73		
		12	30	80	100	35.4	7.4	10	19	13	85		
	58	8	20	50	100	33.2	5.2	6.5	13	6.5	115		
		12	30	80	100	35.4	7.4	10	19	13	129		

Ordering Example Part Number - M - A
HNFJR48 - 12 - 80

Pivot Type



LEMNT (Steel)
LEMNS (Stainless Steel)



RoHS

Tilttable in all 360° directions.

Type	Pad	Thread, Nut
	M Material S Surface Treatment	M Material S Surface Treatment
LEMNT	S45C Trivalent Chromate	SS400 Equivalent Trivalent Chromate
LEMNS	SUS304 -	SUS304 -


Part Number		D	D1	H	ℓ1	ℓ2	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
Type	M-A									LEMNT	LEMNS
LEMNT (Steel)	10-75	32	21	22	6	8	17	11.0	342		
	10-100								351		
	12-75	48	23	29	7.5	10	19	16.0	378		
LEMNS (Stainless Steel)	12-100								390		
	16-100	64	27	32	10	13	24	28.3	430		
	16-130								445		

Ordering Example Part Number
LEMNT16-130

Pivot Short Type



FJRP



RoHS

Thread
M Material: Carbon Steel
S Surface Treatment: Trivalent Chromate

Type	M Material	S Surface Treatment
Main Body	SUS304	
Bottom	Polyamide	

ex Example


When a leg has an angle

When floor surface is curved

Tapped Socket Type




LEMN (Nylon)
LEMT (Steel)
LEMS (Stainless Steel)



RoHS

Type	M Material	S Surface Treatment	Socket	S Surface Treatment
LEMN	Nylon Plastic	-	SUM23	Electroless Nickel Plating
LEMT	Carbon Steel by Mechanical Shading	Electroless Nickel Plating	-	-
LEMS	SUS303	-	SUS303	-

ex Example



Part Number		A	L	D	B	E	Allowable Vertical Load (kN)	Mass (g)	Unit Price
Type	M (Coarse)								
FJRP	6	14	31	25	8	9.7	0.59	11	
	8	19	37.5	30	10	11.2	1.08	21	
	10	20	42.5	40	13	13.7	1.57	38	
	12	25	51	50	17	16	3.14	70	

Ordering Example Part Number
LEMN10

Part Number		B	C	D	E	H	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
Type	M (Coarse)								LEMT	LEMS
LEMN (Nylon)	10	9.5	39.0			16				
	12	12.7	41.0	50	18	19	15.9	17.1		
	16	14.2	44.5			22				

Part Number		H	C	D	B	Allowable Vertical Load (kN)	Mass (g)	Unit Price	
Type	M (Coarse)							LEMT	LEMS
LEMT (Steel)	6	10	14	19	4	3.1	17		
	8	13	18	25	8	4.1	34		
	10	17	22	32	10	15.4	65		
LEMS (Stainless Steel)	12	19	29	48	11	20.5	167		
	16	22	32	64	11	24.6	354		

Kgf (Load)=Nx0.101972