




Shock Absorbing Bumpers

Tapped, Threaded

Bumpers provided with shock and sound absorbing effect, made of soft shock-absorbing material. This product is the replacement for GELMR and GELMF. The bumper part has changed from a 2-layered construction to a 1-layered construction, and the hardness has changed.



Part Number	Type	D	H	L	L1	L2	L3	L4	M	W	R	Unit Price
GELSMR	12	8	22	11	4	3	7	M5 x 0.8	10	2		
	16	10	28	14	5	4	11	M6 x 1.0	14	3		
	20	13	31	17	6	5	14	M8 x 1.25	17	3		
	20A	13	35	17	6	5	14	M8 x 1.25	17	3		
	30	15	39	21	6	5	16	M10 x 1.25 (Fine)	17	3		
	30A	15	44	24	8	5	20	M12 x 1.75	27	3		
			46	26	8	5	22	M14 x 1.5 (Fine)	27	3		

Ordering Example: **Part Number** GELSMR16A

Part Number	Type	D	H	L	L1	L2	L3	M	W	m	f	R	Unit Price
GELSMF	12	8	16	5	4	3	M5 x 0.8	10	8	1.5	2		
	16	10	20	6	5	4	M6 x 1.0	14	10	2	3		
	20	13	26	8	6	5	M8 x 1.25	17	12	2	3		
	30	15	30	10	8	5	M10 x 1.5	27	14	2.5	3		

- Precautions for Use**
- Do not stick or cut with sharpened objects.
 - Do not tear or twist.
 - Insert it only from the vertical direction.
 - Keep away from fire.
 - Do not use detergents.

Characteristic Values of Shock Absorbing Bumpers

Item	Unit	Value
Specific Gravity	-	1.0
Hardness	Asker F	85
Tensile Strength	Mpa	1.15
Elongation	%	680
Heat Resistance	°C	100
Low Temp. Resistance	°C	-10

Elasticity of Shock Absorbing Bumpers




A major characteristic is the three-dimensional slow recovery, the function to recover after compression slowly and in multiple directions. Pressed as thin as shown in the photo and recovers to the original shape gradually after being released from pressure.

Compressive Load Test Results


D	12	16	20	30
30% Compression Load Average (N)	11.1	20.8	35.7	(93)
20% Compression Load Average (N)	6.3	11.6	20.3	51.4
15% Compression Load Average (N)	4.4	8.0	14.1	35.0

*Be aware that using D30 with a compressive load of 20% or over may result in damage.



- Test Conditions**
- Average value measured when compressed by a static load. (Measured 3 times)
- These are not guaranteed values but an example as a set of measured values.
 - The compression rates are for the total length of the bumper part (H + L3).

Drop-Weight Test Data



- Test Conditions**
- Samples: Ø30 x 20 mm
Drop Weight: 16.2 kg
Drop Height: 25 mm
Collision Velocity: 0.71m/s
Testing Instrument: IM10T-30HV (made by IMATEK)
Ambient Temperature: 15°C

- From Test Results**
- Compared with other materials, the shock absorbing bumper results in a much smoother curve from the impact to the peak and the return to normal afterward. This is because the material transmits energy dispersing in multiple directions, while absorbing impact force. From these characteristics, noise reduction effect can be expected. (Please note that results may differ depending on conditions of use.)

