

AIR SUCTION LIFTER

■ Application Use for removing plastic parts and stainless steel parts.

M—GP—SA10 (Cup diameter 10)

M—GP—SA40 (Cup diameter 40)

M—GP—SA50 (Cup diameter 50)



■ Features

- This product can be configured to suction when the valve at hand is opened, and to switch to the blower when the trigger is gripped.
- Can be used for workpieces with rough surfaces.
(E.g.: Brick, wood, paper, urethane foam, etc.)
- It can be used to suction object underwater or used for water suction.
- Hold the trigger to use it as an air blow gun.
- The body is made of sturdy and durable aluminum alloy.

Cup dia.	Cup material	Suction force (kg) (Max. weight)	Weight (g)	Size (L × W × h)	Max. operating temp. (°C)	Inlet	Operating pressure (MPa)	Air consumption (L/min)	Noise value (A characteristic) (dB)	Hose inner dia.	Part Number		Unit Price 1~3 pcs
											Type	No.	
10	Rubber	0.2	300	255×30×55	80	1/4"	0.62	80	73	Use 5 mm or higher	M—GP—SA	10	Quotation
40	Silicone	2.5	330	310×40×55	250							40	
50		3		315×50×55								50	



Order

Part Number

M—GP—SA10



Days to Ship

Quotation



Price

Quotation



Example

