


ENGRAVING PUNCHES

DIE CHECK BUTTONS / SHIMS



H	B	C	Catalog No.		0.1mm increments	A	Characters	Base unit price
			Type	D	L		CHR	1~9 pieces
13	3.3	—	KMCP (1 character)	10	30.0~120.0	5	0 1 2 3 4 5 6 7 8 9 A B C D E F G H I J K L M N O P Q R S T U V W X Y Z	Quotation
	4			10		6		
16	5.3			13		8		
19	6.5			16		10		
23	8.5	20	13					
13	2.5	3.5	KMCPW (2 characters)	10	30.0~120.0	4	RH LH FR FL RR RL	
16	3.3	5		5				
19	4	6		6				
23	5.3	8		8				
28	6.5	10	25	10				
13	2.5	3.5	KMCPWF (Any 2 characters)	10	30.0~120.0	4	0 1 2 3 4 5 6 7 8 9 A B C D E F G H I J K L M N O P Q R S T U V W X Y Z	
16	3.3	5		5				
19	4	6		6				
23	5.3	8		8				
28	6.5	10	25	10				

• KMCPW
RH...RIGHT HAND FR...FRONT RIGHT RR...REAR RIGHT
LH...LEFT HAND FL...FRONT LEFT RL...REAR LEFT

Order

Catalog No.	—	L	—	A	—	CHR
KMCP 13	—	110.0	—	A8	—	G
KMCPWF 16	—	110.0	—	A6	—	AB

Days to Ship


Quotation


Price

Quotation

Alterations

Catalog No.	—	L	—	A	—	CHR	—	(KC-SRC)
KMCP	10	—	80.0	—	A5	—	R	KC90

Alteration	Code	Spec.	1Code
	KC	Addition of key flat to head 90° increments 	Quotation



d	Tie bolt size	M×P	t	Catalog No.		Base unit price 1 ~ 4 pieces
				Type	D	
—	—	M 6×P1.0	—	DCBAW	13	Quotation
11	CB6—20	M 8×P1.25	8	DCBA	16	
13.5	CB8—25	M10×P1.5	10		18	



Order

Catalog No.
DCBA 16

Days to Ship

Quotation

Price

Quotation

Catalog No.	T	Base unit price 1~4 pieces	
		DCIM	DCIMT
DCIM DCIMT	0.05	Quotation	
	0.1		
	0.2		
	0.3		
	0.5		
	1.0		

Order

Catalog No.
DCIM — 0.05

Days to Ship

Quotation

Price

Quotation