


BAND HEATERS

■ Band Heaters




S—MBH

Single



Double



- ① Band Heater
- Insulation Mica
- M Synthetic Mica
- Nichrome Wire
- M Nickel Chrome Ribbon Wire
- ② Tightening Band
- M SUS304
- ③ Leads
- M Heat-resistant Glass Wire

W/cm ² (Watt density)	Type	Part Number		H (Thickness)	W (Watt)	V (Voltage)	L (Wire length)	Unit Price	
		Model	D					1~5 pcs	5~ pcs
$W/cm^2 = W / (D \times H \times 3.14 / 100)$	S—MBH	S (Single)	25~250 (5 mm increments)	25~300 (5 mm increments)	100~	200, 220, 240, 380	300 500 1000 1500 2000 (mm)	Quotation	
		D (Double)							

*Maximum allowable watt density is 5 W/cm²

**When watt is more than 3,000 W, its terminal is changed from wire to thread.

Terminal	Name
	Wire Terminal
	Threaded Terminal



Order



Days to Ship



Price

Part Number — H — W — V — L
S—MBHS50 — 100 — W380 — V220 — L500

Quotation

Quotation