



検具用トグルクランプ ー横抑えー

# TOGGLE CLAMPS FOR CHECKING FIXTURE

-HORIZONTAL HOLD-DOWN-


Fixed Nut-Horizontal Hold-Down Type



(Clamped)

**JQ36202M**

Catalog No.	JQ36202M
Material	SS400
Handle material	PVC (Polyvinyl Chloride)
Surface Treatment	Chromate
Tightening force (N)	892
Weight (g)	113
Stroke (mm)	20
Arm open-close angle	180°
Accessory	Stainless steel bolt
Mounting bolt	M16(P=1.5)




Fixed Nut-Horizontal Hold-Down Type



(Clamped)

**JQ36204M**

Catalog No.	JQ36204M
Material	SS400
Handle material	PVC (Polyvinyl Chloride)
Surface Treatment	Chromate
Tightening force (N)	1333
Weight (g)	270
Stroke (mm)	38
Arm open-close angle	180°
Accessory	Stainless steel bolt
Mounting bolt	M20(P=1.5)




Fixed Nut-Horizontal Hold-Down Type-Long Arm Type




(Clamped)

**JQ36204ML**

Catalog No.	JQ36204ML
Material	SS400
Handle material	PVC (Polyvinyl Chloride)
Surface Treatment	Chromate
Tightening force (N)	1333
Weight (g)	270
Stroke (mm)	38
Arm open-close angle	180°
Accessory	Stainless steel bolt
Mounting bolt	M20(P=1.5)




Fixed Nut-Horizontal Hold-Down Type



(Clamped)

**JQ36224M**

Catalog No.	JQ36224M
Material	SS400
Handle material	PVC (Polyvinyl Chloride)
Surface Treatment	Chromate
Tightening force (N)	3116
Weight (g)	770
Stroke (mm)	66.8
Arm open-close angle	180°
Accessory	Stainless steel bolt
Mounting bolt	M27(P=2.0)



TOGGLE CLAMPS FOR CHECKING FIXTURE



Order

Catalog No.

**JQ101A**



Delivery

**Quotation**