

Product datasheet

Specifications



Controller system, Modicon TM5, Safe logic CPU plus, SERCOS 3 interface, 80 nodes

TM5CSLC200FS

⚠ Discontinued on: Sep 12, 2025 AD

⚠ To be end-of-service on: Dec 31, 2025 AD

⚠ Discontinued

Main

Range of product	Modicon TM5
Product or component type	Controller system
Device application	Safety logic controller
Processor name	Intel Xscale 266 MHz
Reverse polarity protection	Yes

Complementary

Communication network type	SERCOS III (Ethernet)
Transmission rate	100 Mbit/s for full duplex
Cycle time	1 ms
Realtime clock	With non-volatile memory
Number of devices	2 shielded RJ45 1 memory key slot
Function available	Support of 32 machine options With 2 internal switch Support max 100 safety nodes
Maximum cable distance between devices	100 m between station
Rated voltage	24 V -15...20 %
Input protection type	Integrated fuse (not interchangeable)
Power consumption in W	5.1 W
Type of cooling	Fanless
Marking	CE
Safety level	SIL 3 conforming to IEC 61508 SIL 3 conforming to IEC 62061 PL = e conforming to EN 13849-1
Safety reliability data	PFD < 1E-5 PFH < 1E-9 MTTFd > 100 years
Local signalling	1 LED (green or orange) for application run or SoSafe debug mode 1 LED (green) for authorization status 1 LED (orange) for configuration status (Ready) 1 LED (orange) for firmware status 4 LEDs (red) for boot status 1 LED (orange) for memory key status
Colour	Red

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	87.5 mm
Height	99 mm
Depth	75 mm
Net weight	0.29 kg

Environment

Ambient air temperature for operation	0...45 °C (vertical installation) 0...55 °C (horizontal installation)
Ambient air temperature for storage	-25...70 °C
Relative humidity	5...95 % without condensation
IP degree of protection	IP20
Operating altitude	0...2000 m
Standards	IEC 62061 EN 13849-1 IEC 61508 IEC 61131-2 IEC 61511
Product certifications	cULus GOST-R

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.200 cm
Package 1 Width	15.700 cm
Package 1 Length	31.300 cm
Package 1 Weight	510.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	3.890 kg

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	250
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
PVC free	Yes

Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No

Presentation


Safe Logic Controller Module



- (1) Confirmation button
- (2) Selection switch
- (3) Safety processor
- (4) SERCOS III interface
- (5) Integrated power supply
- (6) SERCOS III address switches
- (7) Terminal block for Safe Logic Controller supply
- (8) Ethernet SERCOS III connection with 2 x RJ45 for simple wiring
- (9) Memory Key slot

TM5 Safe Logic Controller


Dimensions




Mounting and Clearance

TM5 Safety System

Spacing Requirements



Mounting on a DIN Rail



Connections and Schema

TM5 System Wiring Recommendations

Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in. 9 0.35 				
mm ²	0,08...2,5	0,25...2,5	0,25...1,5	2 x 0,25...2 x 0,75
AWG	28...14	24...14	24...16	2 x 24...2 x 18