



中国认可
国际互认
检测
TESTING
CNAS L0273

检测报告

委托方名称: 米思米(中国)精密机械贸易有限公司

委托方联络信息: 上海市静安区天目西路 128 号嘉里不夜城企业中心第一座 11 楼

样品名称: 五級防割手套

型号规格: MTGLV-LV5-M

样品描述: 详见图片

样品接收状态: 正常

样品接收日期: 2019-11-06

检测日期: 2019-11-06~2019-11-13

检测地点: 元素成份分析实验室

报告签发日期: 2019-11-13

报告批准:

优尔鸿信检测技术(深圳)有限公司

报告审核:

报告制作:

王新新



LpSxlZGy

检测结果

1. 测试结果:

单位: mg/kg

No.	测试项目	MDL	测试结果					测试方法
			4.1	4.2	4.3	4.4	4.5	
1	镉/Cd	0.5	N.D.	N.D.	N.D.	N.D.	N.D.	(1)
2	铅/Pb	1	N.D.	N.D.	N.D.	N.D.	N.D.	
3	汞/Hg	2	N.D.	N.D.	N.D.	N.D.	N.D.	(2)
4	六价铬/Cr(VI)	8	N.D.	N.D.	N.D.	N.D.	N.D.	(3)
5	一溴联苯/ Monobromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	(4)
	二溴联苯/ Dibromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	三溴联苯/ Tribromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	四溴联苯/ Tetrabromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	五溴联苯/ Pentabromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	六溴联苯/ Hexabromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	七溴联苯/ Heptabromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	八溴联苯/ Octabromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	九溴联苯/ Nonabromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	十溴联苯/ Decabromobiphenyl	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	多溴联苯总和/Sum of PBBs	—	N.D.	N.D.	N.D.	N.D.	N.D.	
6	一溴二苯醚/ Monobromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	二溴二苯醚/ Dibromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	三溴二苯醚/ Tribromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	四溴二苯醚/ Tetrabromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	五溴二苯醚/ Pentabromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	六溴二苯醚/ Hexabromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	七溴二苯醚/ Heptabromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	

检测结果

6	八溴二苯醚/ Octabromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	(4)
	九溴二苯醚/ Nonabromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	十溴二苯醚/ Decabromodiphenyl ether	5	N.D.	N.D.	N.D.	N.D.	N.D.	
	多溴二苯醚总和/ Sum of PBDEs	—	N.D.	N.D.	N.D.	N.D.	N.D.	
7	BBP	30	N.D.	N.D.	N.D.	N.D.	N.D.	(5)
8	DBP	30	N.D.	N.D.	N.D.	N.D.	N.D.	
9	DEHP	30	N.D.	N.D.	N.D.	N.D.	N.D.	
10	DIBP	30	N.D.	N.D.	N.D.	N.D.	N.D.	

测试方法:

- (1) Cd/Pb :样品处理及测试参考 IEC62321-5:2013 &US EPA6010D: 2018;用 ICP-OES 分析
- (2) Hg :样品处理及测试参考 IEC62321-4:2013+A1:2017 &US EPA6010D:2018;用 ICP-OES 分析
- (3) Cr(VI) :样品处理及测试参考 IEC62321-7-2:2017&US EPA7196A:1992; 用 UV-Vis 分析
- (4) PBBs/PBDEs:样品处理及测试参考 IEC62321-6:2015&US EPA 8270E:2018; 用 GC-MS 分析
- (5) BBP/DBP/DEHP/DIBP: 样品处理及测试参考 IEC62321-8:2017&US EPA 8270E:2018; 用 GC-MS 分析


备注:

- (1) N.D. = Not Detected (未侦测出) (<MDL)
- (2) mg/kg = ppm
- (3) MDL = Method Detection Limit (方法侦测极限)
- (4) 样品图片见下页

分析人员:黄斌、温月

检测结果


2. 样品图片:



检测结果

3.测试流程图:

RoHS 10 项 检测流程图



报告结束

注:

- 1.本实验室是中国合格评定国家认可委员会 (CNAS) 认可实验室, 证书编号为: CNAS L0273。
- 2.本报告中的数据结果供科研、教学、企业内部质量控制、产品研发等目的用, 对社会不具有证明作用。
- 3.本检测报告仅对送检样品负责。
- 4.样品及样品信息由申请客户提供。
- 5.未经本实验室书面批准, 不得部分复制此报告。
- 6.检测报告无批准人签字及未加盖公司报告章无效。