





GLOVES FOR INJECTION / GLOVES FOR DIECASTING

■Usage Used in operations with high temperature.

<p>M—HML Gloves for injection (~230°C)</p>  <p>M Cloth material : Cotton Grip : Nitrile Rubber</p>	
<p>M—HMM Gloves for injection (~260°)</p>  <p>M Cloth material : Cotton / Kevlar Grip : Nitrile Rubber</p>	
<p>M—HMH Gloves for diecasting (~593°C)</p>  <p>M Cloth material : Amorphous Silica Fiber Inner : Wool Cushion</p>	

M-HML: Use these gloves during the maintenance of screw, nozzle and band heater.

M-HMG: In addition to the above, these gloves are Kevlar blended, resulting in high function gloves with the same resistance properties as cut-resistant gloves.

M-HMH: These heat resistant gloves are for diecasting operation. Use them according to the temperature level.

L (mm)	A (mm)	B (mm)	C (mm)	Part Number		Unit Price
				Type	Size	
235	185	50	115	M—HML (~230°C)	S	Quotation
265	210	55	115		M	
225	185	40	110	M—HMM (~260°C)	S	
265	210	55	110		M	
270	210	60	140	M—HMH (~593°C)	S	
350	220	130	155		M	
580	350	230	170		L	



Part Number

M—HMM—S



Days
To Ship

Quotation



Price

Quantity Discount Rate

Order Quantity	Standard Service				Non-Standard Service - Large Quantity
Quantity	1	2~4	5~9	10~20	21~
Rate	Standard	5%	10%	15%	To be quoted

⚠ Please check with our WOS for the purchase order that exceeds the displayed quantity.