



HOSE NIPPLES / L-SHAPED SWIVEL HOSE NIPPLES

-SPANNER TYPE-


-HEAT RESISTANCE 120°C TYPE-



Max. pressure MPa (kgf/cm ²)	For hose		L	Allen side B	H	Tapered thread R(PT)	l	Part Number		Unit Price 1-9 pcs
	a	d1						Type	No.	
1.0 (10)	12	6	38	14	7	1/8	10	NPW		1
		8								2
	15	10	48	17	8	3/8	12			3



Max. pressure MPa (kgf/cm ²)	For hose			D	Allen side B	H	Tapered thread R(PT)	l	S	d	Part Number		L	Unit Price (1-9 pcs)		
	a	d1	E								Type	No.		L50	L100	L150
1.0 (10)	12	6	21	10.5	14	7	1/8	10	3.97	9.728	NPL		50 100 150	Quotation		
		8		13.8												
	15	10	28	16.8	17	8	3/8	12	6.35	16.662						



Max. pressure MPa (kgf/cm ²)	For hose		L	L ₂	Allen side B	Hexagonal wrench socket d	Tapered thread R(PT)	l ₁	Part Number		Unit Price 1-9 pcs		
	D	l							Type	No.			
1.0 (10)	12.6	22.5	35.5	16.5	20	○6	1/8	9.5	LSNM		1		
			38.5			○8	1/4	12.5			2		
			39.5			○8	3/8	13.5			3		
			36.5	15.75	19	○5	1/8	9.5			LSN		1
			39.5			○6	1/4	12.5					2
			42.5			○6	3/8	13.5					3

Keep water temperature under 120°C.



Part Number
NPW 1
LSN 2

Part Number — L
NPL1 — 100




Quotation



Quotation



The L-shaped swivel is intended for direction conversion when it is installed on the mold. Note that if you carry out direction conversion continuously by opening and closing the mold, for example, during molding, the O-ring will deteriorate, resulting in water leakage.



COMPONENTS FOR MOLD COOLING AND TEMPERATURE CONTROLLING SYSTEMS