

NEW

PNEUMATIC GRIPPER FOR CLAMPING


PNEUMATIC GRIPPER FOR CLAMPING

■ Pneumatic Gripper for Clamping




M Material	S Surface treatment
Aluminum product	Anodizing

MGFR1



MGFR2



- ⓘ This product's function is a pick-and-place component and is used for the installation of Grip fixtures. Note that it may not be compatible to assemble with other products.
- ⓘ When tightening, the gap is controlled to be less than 1mm.
- ⓘ The surface is anodized, and the color of the actual product may vary from the product picture.
- ⓘ For product attached with body, the gasket is made of silicone.

Part Number		I	A	B	C	D	E	F	G	H	J	M	N	O	P	Q	R
Type	No.																
MGFR	1 (Without body)	14	14	12	10.5	49.5	5.5	14	2	72	12	M12×1	—	—	—	—	—
		20	20	17.5	9	76.5	8	20	2.5	103	17	M17×1	—	—	—	—	—
		30	30	25	12	111	11	29	4	148	27	M27×1	—	—	—	—	—
	2 (With body)	14	14	12	10.5	49.5	5.5	14	2	72	12	M12×1	11	32	19	14	19
		20	20	17.5	9	76.5	8	20	2.5	103	17	M17×1	15	43.5	25	20	27.5
		30	30	25	12	111	11	29	4	148	27	M27×1	20	63	37	30	40

Part Number	Pressure range	Temperature range	Stroke	Piston hole	Closing torque at a pressure of 6 bar	Circulating air consumption	Weight (g)
MGFR1-14	2.5-8 bar	-10~70°C	95°	10mm	19N · cm	1cm ³	25
MGFR1-20				16mm	70N · cm	3.52cm ³	80
MGFR1-30				25mm	300N · cm	12.9cm ³	193
MGFR2-14				10mm	19N · cm	1cm ³	30
MGFR2-20				16mm	70N · cm	3.52cm ³	100
MGFR2-30				25mm	300N · cm	12.9cm ³	300



Order

Part Number — I
MGFR1 — 14



Price

Quotation





Days to Ship

Quotation



Example



REMOVAL RELATED PRODUCTS