

Extruded Brackets - For 3 or More Slots


For 8 Series (Slot Width 10mm) Aluminum Extrusions




Post-Assembly Insertion Easy Brackets

For 8 Series (Slot Width 10mm) Aluminum Extrusions





Part Number Ma		Applicable Screw, T Nut				Allowable Load	Unit Price	Volume Discount Rate
Part Number	(g)	Screw	Quantity	T Nut	Quantity	(N)	1~99 pc(s).	100~200
NBLUT8	564	CBM8-25	6	HNTT8-8	6	5292		
HBLUT8								




Features: Brackets to connect Extrusions with 4 slots (HFS8-40160 etc.) with one bracket. ■Brackets for Heavy Load NBLUQ8 A6063S-T5 A6N01SS-T5

8-69	Both sides and screw holes of anodized.	NBLUQ8 is not

Part Number Mass		Applicable Screw, T Nut				Allowable Load	Unit Price	Volume Discount Rate
Part Number	(g)	Screw	Quantity	T Nut	Quantity	(N)	1~99 pc(s).	100~200
NBLUQ8	770	CBM8-25	8	HNTT8-8	8	7056		
HBLUQ8								







Alt	terations	Part Number - (C, S) HBLUT8 -	ET, SST, SEU, SSU, SEP, SSP, SEC) SET		
Alterations Code		Spec.	Applicable Bracket		
		Adds taps on a bracket for cover mounting.	NBLUT8		
Mounting Hole	С	(M5 on Both Sides) (Mounting Screw HCBM on P.754)	HBLUT8		
Alteration for					

HBLUQ8


Alterations	Code		Spec).	Applicable Bracket			
	SET SST (Stainless Steel) SEU (Pre-Assembly Insertion)	for fixin	ng the b is come it acket pric en HBLUT	· .				
	Spring Nuts	Code	Screw	Nut				
	Pre-Assembly Insertion Spring Nuts Stainless Steel SEP (Post-Assembly Insertion Spring Nuts	SET CB	M8-25	HNTT8-8	HBLUT8			
Applicable Screws and		SST SC	B8-25	HNTTSN8-8				
Nuts Set			SEU CB	M8-25	HNTU8-8			
		SSU SC	B8-25	SHNTU8-8				
	SSP	SEP CB	M8-25	HNTP8-8	NBLUQ8			
	(Post-Assembly Insertion Spring Nuts) Stainless Steel	SSP SC	B8-25	SHNTP8-8				
		SEC HC	BST8-29	HNTT8-8				
	Screws with Captured Washer and Nuts	• When specifying other than HBLUT8, check for the applicable screws and nuts.			HBLUQ8			
Included So	ncluded Screw is not RoHS compliant when -SET, -SEU or -SEP are specified.							












For aluminum extrusions with 2 slots, brackets can be mounted on both sides.



Tighten a hex socket head cap screw ③ to fix the plate. (Reference Tightening Torque: 15N • m)