
ROLLER PEDESTAL FOR SCREW

SOFT VISE LINER / COPPER VISE CAP

■ Application It is used for cleaning and checking the appearance of screws.



Body size (mm)	Part Number	Unit price
Body Size (IIIII)		1~3 pcs
175×260	M-SHR-4	Quotation

Please check with our WOS for the purchase order that exceeds














■ Features

- The installation width of the 3-step adjustable rollers can be adjusted according to the screw diameter. (Supports screw diameters of φ 25 to 200)
- It can be used for cleaning while placing and turning screws.
 The same applies to checking the appearance of the screw.

Application It is used for fixing screws with a vise.



■ Features

- It has a horizontal V-groove on one side and a V-groove at 45° in the vertical direction on the other side, allowing objects with uneven shapes to be fixed.
- As it has a magnet, it is easy to install onto a vise.

Length (mm)	Part Number	Unit price
Lengur (mm)	Fait Nullibei	1~5 pcs
125	M-VJ500	Quotation

Please check with our WOS for the purchase order that exceeds the displayed quantity.














■ How to use

- Mount the vise liner on a vise and fix the flight of the screw to the groove of the vise liner.
- As it is fixed, screw maintenance can be performed by one person.

■ Application It is used for fixing screws with a vise.



■ Feature:

- $\boldsymbol{\cdot}$ As it is made of copper, it does not easily damage screws.
- As it is fixed, screw maintenance can be performed by one person.
- The copper vise cap is not grooved.

Langeth (mans)	Part Number		Unit price
Length (mm)	Туре	No.	1~2 pcs
75	M-cvc	1	
100		2	otatio
125		3	not
150		4	Ō

Please check with our WOS for the purchase order that exceeds the displayed quantity.









19