
## [Standard] Horizontal Surface Z-Axis, Feed Screw / Linear Ball Slide

S Surface Treatment: Black Anodize




| Part Number |      |      | Stage Surface | Travel Distance | Travel per Rotation | Parallelism | Load Capacity | Weight | Unit Price |  |  |
|-------------|------|------|---------------|-----------------|---------------------|-------------|---------------|--------|------------|--|--|
| TYPE No.    |      | (mm) | (mm)          | (mm)            | (µm)                | (N)         | (kg)          |        |            |  |  |
|             |      | 40   | 40x40         | +5              | 0.5                 | 100         | 29.4          | 0.15   |            |  |  |
|             | ZLTD |      |               |                 |                     |             |               |        |            |  |  |

Fix the bottom plate at 3 points.

Counterclockwise rotation of the knob elevates the stage surface.




**Features:** Z-Axis Stages with the stage top rising/lowering horizontally. Best suited for setup changes and simple focus adjustments.



The micrometer head is only for raising and lowering the positioning stage. The scale and the amount by which the positioning stage is raised and lowered will vary.



## [High Precision] Dovetail Slide, Rack & Pinion / Cross Roller




Inspection

60 60x60



Features: Suitable for highly accurate fine adjustment of horizontal surface of Z-axis. ZLPGS has higher load capacity compared to the same size ZLPG (P.1973)



Standard Stages Similar Products (available for limited sizes only): ZLLB (P.1971)

|  | Communication of the state of t |     |               |                    |               |                 |                              |        |         |                          |        |         |             |                           |            |             |
|--|--|-----|---------------|--------------------|---------------|-----------------|------------------------------|--------|---------|--------------------------|--------|---------|-------------|---------------------------|------------|-------------|
|  | Part Number  |     | Stage Surface | Travel<br>Distance | Load Capacity | Travel Accuracy | y Moment Load Capacity (N·m) |        |         | Moment Rigidity ("/N·cm) |        |         | Parallelism | Weight Accessory (4 pcs.) | Unit Price |             |
|  | Type   | No. | (mm)          | (mm)               | (N)           | Straightness    | Pitching                     | Yawing | Rolling | Pitching                 | Yawing | Rolling | (µm)        | (kg)                      | TypeM-L    | Offit Frice |
|  | ZLPGS 60   | 40  | 40x40         | ±3                 | 29.4          | 3µт             | 1.8                          | 1.1    | 1.2     | 0.81                     | 0.22   | 0.30    | 100         | 0.49                      | SCB3-6     |             |
|  |  | 60  | 60x60         | ±3                 | 58.8          |                 | 3.3                          | 2.4    | 3.1     | 0.42                     | 0.18   | 0.12    |             | 0.99                      | SCB4-6     |             |
|  | ZLPCGS   | 40  | 40x40         | ±3                 | 29.4          | 3µm             | 1.8                          | 1.1    | 1.2     | 0.81                     | 0.22   | 0.30    | 100         | 0.47                      | SCB3-6     |             |
|  |  | 60  | 60x60         | ±3                 | 29.4          |                 | 3.3                          | 2.4    | 3.1     | 0.42                     | 0.18   | 0.12    |             | 0.97                      | SCB4-6     |             |

- Micrometer Head Resolution: 10um/division
- Knob Cover HDCVR15 (Sold Separately): Ø15 micrometer head knobs can be increased in diameter by installing the cover. 🗷 R2004
- The micrometer head is only for raising and lowering the positioning stage. The scale and the amount by which the positioning stage is raised and lowered will vary.



1 -1972 1 -1971

Unit Price